

TECHSPEC[®] 7mm, Uncoated, High Tolerance N-BK7 Right Angle Prism



N-BK7 High Tolerance Right Angle Prisms

Stock **#32-541** 20+ In Stock

-

1

+

C\$130⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$130.90 each
Qty 6-25	C\$104.30 each
Qty 26-49	C\$98.00 each
Need More?	Request Quote

Product Downloads

General	
Right Angle Prism	Type:
Physical & Mechanical Properties	
+0/-0.1	Dimensional Tolerance (mm):
Protective as needed	Bevel:

9.90	Length of Hypotenuse (mm):
7.00	Length of Legs (mm):
Optical Properties	
±15	Angle Tolerance (arcsec):
Uncoated	Coating:
N-BK7	Substrate: ☐
40-20	Surface Quality:
Left-Handed	Image Orientation:
90	Ray Deviation (°):
350 - 2200	Wavelength Range (nm):
1.25	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:

Product Details

• Ray Deviation of 90°


• Left Handed Image

• Low Arcsecond Angle Tolerance

• Additional [Right Angle Prism](#) Options Available


TECHSPEC® High Tolerance N-BK7 Right Angle Prisms are generally used to bend image paths or redirect light at 90°. This process produces a left-handed image, depending on the prism's orientation, the image may be inverted or reverted. Right angle prisms can also be combined for image/beam displacement. TECHSPEC® High Tolerance N-BK7 Right Angle Prisms feature low arcsecond angle tolerance and are made from precision N-BK7 for use in a variety of visible light applications. These prisms are available uncoated, with a protective aluminum overcoat, or VIS° & aluminized.

Technical Information





Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram