

[See all 30 Products in Family](#)

TECHSPEC®

7X, 1064nm Scorpii® Nd:YAG Beam Expander



7X, 1064nm LCht Fixed YAG Beam Expander, #37-063

Stock **#37-063**

CONTACT US

-

1

+

C\$288⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-9	C\$288.40 each
Qty 10-24	C\$259.00 each
Qty 25-99	C\$228.20 each
Need More?	Request Quote

Product Downloads

General	
Beam Expander	Type:
Fixed Magnification	Style:
Physical & Mechanical Properties	
78.20	Length (mm):

75	Weight (g):
29.95	Housing Diameter (mm):
Optical Properties	
3.5	Entrance Aperture (mm):
21	Exit Aperture (mm):
7X	Expansion Power:
Optical Glass	Substrate: ☐
>96 (nominal)	Transmission (%):
0	Angle of Incidence (°):
NIR II (750-1550nm)	Coating:
1064	Design Wavelength DWL (nm):
<λ/4 @ 1064nm for Input Beam ≤1.6mm (by design)	Transmitted Wavefront, P-V:
1064	Wavelength Range (nm):
R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm	Coating Specification:
None	Divergence Adjustment:
Threading & Mounting	
M22 x0.75	Mounting Threads:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- AR Coated for Nd:YAG Laser Wavelengths: 355nm, 532nm, and 1064nm
- Fixed Magnifications Available from 2X to 10X
- Designed for OEM Integration without Divergence Adjustment

TECHSPEC® Scorpii® Nd:YAG Beam Expanders are designed for beam expansion applications such as laser engraving and material processing. These beam expanders feature AR coatings and high transmissions. AR coated for the Nd:YAG laser wavelengths 355nm, 532nm, and 1064nm, these beam expanders are available in multiple fixed magnifications from 2X to 10X with M22 x0.75 threading. TECHSPEC Scorpii Nd:YAG Beam Expanders are a cost-effective solution for system integration. Ideal for OEM quantities, these beam expanders can quickly meet prototyping and application timelines.

TECHSPEC Scorpii® Nd:YAG Beam Expander Kits are also available. For HeNe laser applications, TECHSPEC Arcturus® HeNe Beam Expanders are available. For applications where rotating optics are acceptable, the TECHSPEC Vega® Laser Line Beam Expanders and TECHSPEC Vega® Broadband Beam Expanders are available. For higher precision applications where sliding optics are necessary, please see our TECHSPEC Draconis® Nd:YAG Laser Line Beam Expanders or TECHSPEC Draconis® Broadband Beam Expanders. For broadband or ultrafast applications, TECHSPEC Canopus® Reflective Beam Expanders are available.

532nm versions are compatible with popular 530nm laser applications, and 1064nm versions are ideal for use with laser applications at 1060nm, 1070nm, and 1075nm.



