

## 8" Length, 1/4-20 and 1/4-20, Steel Post



Stock #72-798 **NEW** 20+ In Stock

- 1 + C\$14.<sup>70</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$14.70 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

English **Type:**

### Physical & Mechanical Properties

203.20 ±0.1 **Length (mm):**

8 **Length (inches):**

12.70 -0.02/-0.05 **Diameter (mm):**

**Diameter (inches):**

## Threading & Mounting

Thread 1: 1/4 - 20  
Thread 2: 1/4 - 20

**Male Thread:**

## Regulatory Compliance

**Compliant**

**RoHS 2015:**

**View**

**Certificate of Conformance:**

**Compliant**

**Reach 247:**

## Product Details

- English or Metric Versions Options Available
- Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
- Removable Top and Bottom Set Screws Available

Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x 0.7/M6 x 1.0 for Metric; 8-32<sup>1/4</sup>-20 for English) are laser-engraved on the ends of each post for quick identification and integration.

**Note:** All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" key size, or other tools to rotate the post easily.