

TECHSPEC® 75mm Dia. x 150mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#33-925** ☐ In Stock
[Other Coating Options](#)

1 **C\$507.50**

ADD TO CART

Qty 1-5
C\$507.50
Qty 6+
C\$406.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
75.00 +0.0/-0.025

Effective Focal Length EFL (mm):
150.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 126.46
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 73.5
Centering (arcmin): <1
Center Thickness CT (mm): 46.30 ±0.20
Center Thickness CT 1 (mm): 23.2 ±0.10
Center Thickness CT 2 (mm): 23.1 ±0.10
Radius R₁ (mm): 92.05
Radius R₂ (mm): -72.85
Radius R₃ (mm): -305.87
Edge Thickness ET (mm): 36.01
Substrate: ☐ N-BAK1 / N-SF8
Surface Quality: 40-20
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View