

## 808nm High Performance Laser Line Filter 25mm Dia.



High Performance Laser Line Bandpass Filters

Stock **#64-258** **1 In Stock**

☐ [Additional Bandwidths](#)

-

1

+

C\$1,192<sup>80</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | C\$1,192.80 each              |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                           |
|----------------------------------|---------------------------|
| Bandpass Filter                  | Type:                     |
| Physical & Mechanical Properties |                           |
| 25.00 +0.0/-0.1                  | Diameter (mm):            |
| ≥22                              | Clear Aperture CA (mm):   |
| ±0.10                            | Thickness Tolerance (mm): |

|                                                                           |                                       |
|---------------------------------------------------------------------------|---------------------------------------|
| Mounted in Black Anodized Ring                                            | Construction:                         |
|                                                                           |                                       |
| ML-C-48497A<br>Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3 | Physical Durability:                  |
|                                                                           |                                       |
| 2.0 ±0.1                                                                  | Substrate Thickness (mm):             |
| Optical Properties                                                        |                                       |
| 0 ±2                                                                      | Angle of Incidence (°):               |
|                                                                           |                                       |
| 3.1                                                                       | Bandwidth (nm):                       |
| <11                                                                       | Beam Deviation (arcsec):              |
|                                                                           |                                       |
| 626 - 800 & 816 - 1270                                                    | OD 5 Blocking Wavelength Range (nm) : |
| 743 - 796 & 820 - 889                                                     | OD 6 Blocking Wavelength Range (nm):  |
| ≥6.0                                                                      | Optical Density OD (Average):         |
| 808.00                                                                    | Center Wavelength CWL (nm):           |
| 808                                                                       | Design Wavelength DWL (nm):           |
| 3.07 - 5.66                                                               | Full Width-Half Max FWHM (nm):        |
| Fused Silica                                                              | Substrate: □                          |
| >90                                                                       | Minimum Transmission (%):             |
| Hard Coated                                                               | Coating:                              |
| 60-40                                                                     | Surface Quality:                      |
| >90                                                                       | Transmission (%):                     |
| 626 - 800 & 816 - 1270                                                    | Blocking Wavelength Range (nm):       |
| ¼ @ 633nm                                                                 | Transmitted Wavefront, P-V:           |
| Threading & Mounting                                                      |                                       |
| 3.5 ±0.1                                                                  | Mount Thickness (mm):                 |
| Environmental & Durability Factors                                        |                                       |
| <5                                                                        | Temperature Dependence (ppm/°C):      |
| ML-STD-810F<br>Paragraphs 501.4, 502.4, and 507.4                         | Environmental Durability:             |
| Regulatory Compliance                                                     |                                       |
| Compliant                                                                 | RoHS 2015:                            |
| Compliant                                                                 | Reach 209:                            |
| View                                                                      | Certificate of Conformance:           |

## Product Details

- Over 90% Transmission at Specified Laser Lines
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, High Performance Laser-Line Bandpass Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. These laser line filters are available at popular diode and Nd:YAG laser lines, including 532nm, 785nm, and 1064nm. High Performance Laser-Line Bandpass Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, High Performance Laser-Line Bandpass Filters are excellent complements to TECHSPEC® Notch Filters and [Laser Line Longpass Filters](#).

**Note:** These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). Atypical LIDT for these filters is 0.1 J/cm<sup>2</sup> @ 532nm, 10ns.

## Technical Information



## Compatible Mounts