

75mm FL, 1064nm Edmund Optics® F-Theta Lens



Stock **#15-178** CLEARANCE [CONTACT US](#)

- 1 + **C\$743.33**

ADD TO CART

Qty 1+
C\$743.33

Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm):
1064

Focal Length FL (mm):
77.03

Maximum Diameter (mm):
68

Scan Angle (°):
±18.60

Scan Field (mm):
35.4 x 35.4

Mounting Threads: M60 x 1.0
Telecentricity (°): <7
Transmission (%): ≥95
Type: F-Theta Lens
Working Distance (mm): 72.1
Wavelength Range (nm): 1064
Range Distance (mm): 104.9
Focus Size Diameter, 1/e² (μm): 13
Input Beam Diameter, 1/e² (mm): 12
Maximum Length (mm): 54.4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View