

## 830 Grooves/mm, 50mm Sq, UV Transmission Grating Beamsplitter



Stock **#85-299** ☐ In Stock

-

1

+

C\$462.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| C\$462.00                     |
| Qty 10+                       |
| C\$415.80                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Groove Density (grooves/mm):  
830

Wavelength Range (nm):  
250 - 450

Blaze Angle (°):  
19.4

|                                                                                                                                                    |
|----------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Dimensions (mm):</b><br>50.00 x 50.00                                                                                                           |
| <b>Construction:</b><br>Blazed Grating                                                                                                             |
| <b>Length (mm):</b><br>50.00                                                                                                                       |
| <b>Substrate:</b> <br><a href="#">Fused Silica</a> (Corning 7980) |
| <b>Thickness (mm):</b><br>2.00 ±0.5                                                                                                                |
| <b>Type:</b><br>Transmission Diffraction Grating                                                                                                   |
| <b>Width (mm):</b><br>50.00                                                                                                                        |
| <b>Alignment of Grooves to Edge (°):</b><br>±0.5                                                                                                   |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |