

[See all 12 Products in Family](#)

## 850nm, Ethernet High Intensity Coaxial Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination Ethernet Controlled High Intensity LED Spot Lights

Stock #21-361 **1 In Stock**

C\$791.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	C\$791.00 each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

SL162-850C1	<b>Model Number:</b>
50,000	<b>LED Lifetime (hours):</b>
1	<b>Number of LEDs:</b>
LED Illuminator	<b>Type of Illumination:</b>

**Note:**  
Required Controller [#18-645](#); Required Power Supply [#66-855](#)

**Manufacturer:**  
Advanced Illumination

**Geometry:**  
Spot Light

**Illumination Mode:**  
Constant, Pulsed, Gated

## Physical & Mechanical Properties

**Weight (g):**  
85.1

## Optical Properties

**Color:**  
IR

**Wavelength (nm):**  
850

## Hardware & Interface Connectivity

**Connector:**  
C1

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#66-855](#)  
Europe: [#66-855](#)  
Japan: [#89-513](#)  
Korea: [#33-773](#)  
China: [#66-855](#)

**Length of Cable (m):**  
2

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +60

## Regulatory Compliance

**RoHS 2015:**  
[Exempt](#)

**Reach 224:**  
[Contains SVHC\(s\)](#)

**Certificate of Conformance:**  
[View](#)

## Product Details

- Controllable via Ethernet GUI or Web Browser
- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Ports
- Efficient Thermal Management for Long LED Life
- Compatible with [TECHSPEC® Telecentric Backlight Illuminators and Lenses](#)

Advanced Illumination Ethernet Controlled High Intensity In-Line Lights utilize a C1 connector to connect to the DCS-100E Single Output Controller ([#18-645](#)). The DCS-100E Single Output Controller allows these high intensity in-line lights to be ethernet controlled through a downloadable software package or through a Web Based Graphical User Interface (GUI). With efficient thermal management, these in-line lights are able to provide 33,000 Lux at a working distance of 100mm with a spot size of 61mm in either a continuous, pulsed, or gated operating mode. Advanced Illumination Ethernet Controlled High Intensity In-Line Lights can be overdriven in short pulses without damaging the LED through Advanced Illumination's SignaTech™ Control System which is available with the DCS-100E Controller. These lights are available in UV, Blue, Green, Red Orange, IR, or White and are compatible with the 8mm port found on many in-line illumination imaging lenses, making them an excellent choice for use with TECHSPEC® Telecentric Backlight Illuminators and telecentric lenses with an [inline illumination port](#). For applications that do not require ethernet controlled functionality, [Advanced Illumination High Intensity In-Line Lights](#) are also available.

**Note:** 24V power supply ([#66-855](#)) and DCS-100E Single Output Controller ([#18-645](#)) are required for use.