

[See all 26 Products in Family](#)

TECHSPEC® 76.2mm Dia., 12.7mm Thick, Fused Silica Uncoated Laser Grade Substrate



TECHSPEC® Uncoated Laser Window Substrates

Stock #14-844 **3 In Stock**

⊖ 1 ⊕ C\$763⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	C\$763.00 each
Qty 11-25	C\$672.00 each
Qty 26-50	C\$596.40 each
Need More?	Request Quote

Product Downloads

General

Laser Window Substrate **Type:**

Physical & Mechanical Properties

12.70 ±0.20 **Thickness (mm):**

68.58 **Clear Aperture CA (mm):**

76.20 +0.00/-0.10	Diameter (mm):
90	Clear Aperture (%):
M10	Back Surface:
<3	Parallelism (arcmin):
Protective as needed	Bevel:
Fine Ground	Edges:

Optical Properties

Fused Silica (Corning 7980 0A)	Substrate: <input type="checkbox"/>
1.458	Index of Refraction (n_d):
10-5	Surface Quality:
Uncoated	Coating:
67.8	Abbe Number (v_d):
200 - 2200	Wavelength Range (nm):
M10	Surface Flatness (P-V):

Material Properties

7980 0A	Fused Silica Grade:
---------	----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Up to 10-5 Surface Quality and M10 Surface Flatness Available
- Fused Silica or N-BK7 Material
- Standard Imperial Sizes for Drop-in Replacement Solutions
- [Laser Line Coated Versions](#) Available
- [Mirror Substrates](#) Also Available

TECHSPEC® Uncoated Laser Window Substrates are laser quality window substrates designed to be used in demanding laser applications. These laser window substrates are available, manufactured from fused silica for high power laser applications that require excellent thermal stability or from N-BK7 for more cost sensitive laser applications. Both the fused silica and N-BK7 laser window substrates feature precision grade M10 surface flatness and 10-5 surface quality, ensuring minimal disturbance to transmitted beams. TECHSPEC® Uncoated Laser Window Substrates are available in standard imperial sizes from 12.7 to 50.8mm in diameter for the convenience of drop-in replacement into existing laser systems. Custom dimensional and coating options are available, please contact us for custom inquiries.