

[See all 64 Products in Family](#)

Coherent® StingRay™ Line Generator 1231519 | 785nm, 50mW, 60° Fan Angle

See More by [Coherent®](#)



Stock **#86-877** [CONTACT US](#)

-

 1

+

C\$1,337^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,337.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

Coherent®
Manufacturer:

Diode
Type of Laser:

IIIb
Laser Class - CDRH:

1231519	Model Number:
Physical & Mechanical Properties	
<10	Pointing Stability (μrad/°C):
97.80	Length (mm):
Optical Properties	
TEM ₀₀	Spatial Mode:
785.00	Wavelength (nm):
<1.5	Mode Quality, M ² :
±19	Wavelength Tolerance (nm):
Infrared	Color:
60.00	Fan Angle (°):
Electrical	
50	Output Power (mW):
Max Analog: 500	Modulation Frequency (kHz):
Hardware & Interface Connectivity	
Power Supply: Power Supply Required and Sold Separately. USA: #86-878 Europe: #86-878 Japan: #86-878 Korea: #86-878 China: #86-878	
Electrical Leads/ Pin Connections: Hirose HR-10P-12S	
Free Space	Output Type:
5 - 24 DC	Input Voltage (V):
Environmental & Durability Factors	
-10 to +50	Operating Temperature (°C):
-20 to +60	Storage Temperature (°C):
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

For CDRH certified systems, class IIIb lasers require [#86-878](#). These lasers include a Hirose connector and flying lead terminals for compatibility with a variety of power supplies.

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- [Coherent® StingRay™ Developer's Kit](#) also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High

precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

Note: For CDRH certified systems (Class IIIb), [#86-878](#) Laser Controller and additional external voltage source (0.5-5V) with BNC connector is required.