

78mm Standard UV Fixed Focal Length Lens



78mm Standard UV Fixed Focal Length Lens, #57-543

Stock **#57-543** 2 In Stock

-

1

+

C\$7,532⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$7,532.00 each
Need More?	Request Quote

Product Downloads

General	
UV Fixed Focal Length Lenses	Series:
C-Mount adapter can be removed for use with M42 x 75 (T2-Mount) cameras	Note:
Fixed Focal Length Lens	Type:
Physical & Mechanical Properties	
Variable	Iris Option:

109.30	Length (mm):
62.5	Maximum Diameter (mm):
62.5	Outer Diameter (mm):

446.00	Weight (g):
--------	-------------

Optical Properties

36.1	Field of View @ Min Working Distance (mm):
36.1mm - 4.4°	Horizontal Field of View, 1/2" Sensor:

16.00	Maximum Image Circle (mm):
-------	----------------------------

78.00	Focal Length FL (mm):
-------	-----------------------

440 - ∞	Working Distance (mm):
---------	------------------------

f/3.8 - f/16	Aperture (f/#):
--------------	-----------------

UV-NIR	Lens Wavelength Range:
--------	------------------------

Sensor

1"	Maximum Sensor Format:
----	------------------------

Threading & Mounting

M49.0 x0.75	Filter Thread:
-------------	----------------

C-Mount	Mount:
---------	--------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- 1", C-Mount Lens
- Spectral Range of 230 - 1200nm
- 25mm to 78mm Focal Lengths

UV Fixed Focal Length Lenses are ideal for use in a variety of applications, including the surface inspection of circuits or fiber optics, quality control of semiconductor materials, or for locating oil contamination or leakage. Additional applications include forensic, pharmaceutical, or biomedical imaging, fluorescence, security, or counterfeit detection. UV Fixed Focal Length Lenses are manufactured from fused silica elements to provide excellent transmission from the ultraviolet to the near-infrared.

Note: These lenses are not corrected for chromatic aberration, and require refocusing when using an illumination source with a spectral bandwidth greater than 10nm. A monochromatic light source and narrow bandpass filter are recommended to improve the overall performance of the lens. The 78mm lens ([#57-543](#)) has a removable C-mount adapter, enabling it to be used with M42 x0.75 (T2) mounts.

Technical Information

