



[See all 4 Products in Family](#)

Richardson Gratings™ 79 Grooves, 25 x 50mm, 63° Blaze Angle, Echelle Grating

See More by [Richardson Gratings™](#)



Stock **#15-742** 6 In Stock

-

1

+

C\$441^{.00}

ADD TO CART

Volume Pricing	
Qty 1-9	C\$441.00 each
Qty 10-24	C\$396.90 each
Need More?	Request Quote

Product Downloads

General	
Type:	Echelle Grating
Master Reference:	401E
Physical & Mechanical Properties	
Dimensions (mm):	

25.0 x 50.0 ±0.1	
>90	Clear Aperture (%):
Ruled Grating	Construction:
50.00	Length (mm):
6.00 ±0.5	Thickness (mm):
25.00	Width (mm):
±1	Centering of Ruled Area on Substrate (mm):
±0.15	Alignment of Grooves to Edge (°):
<0.05	Groove Spacing Tolerance (%):

Optical Properties	
79	Groove Density (grooves/mm):
All	Blaze Wavelength (nm):
63	Blaze Angle (°):
Aluminium	Coating:
Float Glass	Substrate: ☐
λ/4	Reflected Wavefront, RMS:
Unpolarized	Polarization:
1	Spectral Order (m):

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Highest Resolving Power and Dispersion
- Low Groove Density for Use in Higher Orders
- Groove Spacing Tolerance <0.05%
- Custom Sizes Available

Richardson Gratings™ Echelle Reflective Diffraction Gratings feature superior resolving power and dispersion compared to other reflective diffraction gratings. These gratings are characterized by coarse groove spacings, relatively low groove densities and high blaze angles. They are suitable for use from near-UV wavelengths to the infrared (~20µm). Richardson Gratings™ Echelle Reflective Diffraction Gratings are ideal for applications such as compact high resolution spectrometers with high angular dispersion and throughput. Custom sizes are available on request.

Note: The surface of these gratings is very sensitive and should never be touched when handling the optic. If cleaning is required to remove dust particles, non-contact cleaning using clean compressed air is recommended.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

