

[See all 28 Products in Family](#)

## 8" x 4", Red 625nm, UltraSeal Washdown Backlight

See More by [Advanced Illumination](#)



Advanced Illumination UltraSeal Washdown Backlights

Stock **#90-789** NEW CONTACT US

⊖ 1 ⊕ C\$2,464<sup>00</sup>

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,464.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Model Number:**  
BL245-0804625ICSS

**LED Lifetime (hours):**  
50000

**Type of Illumination:**  
LED Illuminator

**Note:**  
Optional Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are Available

Advanced Illumination

Manufacturer:

Backlight

Geometry:

Constant

Illumination Mode:

## Physical & Mechanical Properties

223.8 x 122.2 x 24.0

Dimensions (mm):

635

Weight (g):

8 x 4

Active Area (inches):

## Optical Properties

Red

Color:

625

Wavelength (nm):

## Electrical

0.96A

Minimum Input Current:

## Hardware & Interface Connectivity

Flying Leads

Connector:

24V

Input Voltage (V):

Power Supply:

Power Supply Required and Sold Separately.

USA: [#66-855](#)

Europe: [#66-855](#)

Japan: [#89-513](#)

Korea: [#33-773](#)

China: [#66-855](#)

## Environmental & Durability Factors

0 - 60

Operating Temperature (°C):

IP69K

Environmental Rating:

## Regulatory Compliance

[View](#)

Certificate of Conformance:

## Product Details

- IP69K Certified for Extreme Washdown Environments
- Stainless Steel Housing
- Intensity Output up to 15,000 Lux
- Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended

Advanced Illumination UltraSeal Washdown Backlights offer intense, even illumination up to 15,000 Lux while providing maximum protection in extreme environmental conditions. These IP69K certified backlights feature a crevice-free design to withstand high temperature washdown procedures and material buildup. The 316 stainless steel is FDA compliant, making them a suitable option for food or pharmaceutical inspection environments. Advanced Illumination UltraSeal Washdown Backlights are ideal for hygienic and aseptic manufacturing applications, such as prolonged liquid immersion and high-pressure steam cleaning common in food and beverage inspection and processing.

**Note:** Requires 24V power supply [#66-855](#). Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are recommended and sold separately.