


TECHSPEC® 800nm, 12.5 x 17.6mm, Dichroic Longpass Filter



Stock **#69-883** ☐ In Stock

-

1

+

C\$175.00

ADD TO CART

Qty 1-5
C\$175.00
Qty 6+
C\$140.00
Volume Pricing
Request Quote

Get Product Downloads



Dimensions (mm):
12.5 x 17.6

Angle of Incidence (°):
45

Cut-On Wavelength (nm):
800.00

Substrate: ☐

Fused Silica (Corning 7980)
Length (mm): 17.60
Coating: Hard Coated
Reflection (%): >97, Average Polarization >95, Absolute Polarization
Reflection Wavelength (nm): 600 - 760
Surface Quality: 60-40
Thickness (mm): 1.05
Thickness Tolerance (mm): ±0.1
Transmission (%): >85, Average Polarization >80, Absolute Polarization
Transmission Wavelength (nm): 830 - 1600
Type: Dichroic Filter
Width (mm): 12.50
Dimensional Tolerance (mm): +0.0/-0.2
Transmitted Wavefront Tolerance: λ/4
Cut-On Tolerance (%): ±2
Slope Factor (%): 3.00
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497ASection 4.5.4.2
Wavelength Range (nm): 600 - 1600
Wavelength Range (μm): 0.6 - 1.6

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant