


TECHSPEC<sup>®</sup> 800nm, 12.7mm Dia. x 6.35mm Thickness, Ultrafast Laser Mirror



Stock **#26-829** [CONTACT US](#)

-

1

+

C\$147<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | C\$147.00 each                |
| Qty 6-25       | C\$130.90 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                     |
|----------------------------------|---------------------|
| Laser Mirror                     | Type:               |
| Physical & Mechanical Properties |                     |
| 6.35 ±0.20                       | Thickness (mm):     |
| 12.70 +0.00/-0.10                | Diameter (mm):      |
| 90                               | Clear Aperture (%): |

|                                                                                                                                   |                             |
|-----------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| Commercial Polish                                                                                                                 | Back Surface:               |
| <3                                                                                                                                | Parallelism (arcmin):       |
| Optical Properties                                                                                                                |                             |
| Fused Silica (Corning 7980)                                                                                                       | Substrate: □                |
| 10-5                                                                                                                              | Surface Quality:            |
| 45                                                                                                                                | Angle of Incidence (°):     |
| Ultrafast (750-850nm)                                                                                                             | Coating:                    |
| 800                                                                                                                               | Design Wavelength DWL (nm): |
| 750 - 850                                                                                                                         | Wavelength Range (nm):      |
| λ/8                                                                                                                               | Surface Flatness (P-V):     |
| Coating Specification:<br>R <sub>(avg)</sub> S & P >99.90% @ 800nm @ 45° AOI<br>R <sub>(avg)</sub> >99.7% @ 770 - 830nm @ 45° AOI |                             |
| Dielectric                                                                                                                        | Coating Type:               |
| GDD Specification:<br>±10 fs <sup>2</sup> @ 750 - 850nm @ 45° AOI (s-pol)<br>±20 fs <sup>2</sup> @ 770 - 830nm @ 45° AOI (p-pol)  |                             |
| Environmental & Durability Factors                                                                                                |                             |
| ML-PRF-13830B                                                                                                                     | Durability:                 |
| Regulatory Compliance                                                                                                             |                             |
| View                                                                                                                              | Certificate of Conformance: |

## Product Details

- GDD as Low as ±20fs<sup>2</sup> at Design Wavelength Range
- Greater than 99.9% Reflectivity
- Ideal for Ti:sapphire and Yb:doped Ultrafast Lasers

TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors feature a multilayer dielectric coating on fused silica substrates for excellent reflectivity of greater than 99.9%, and low coefficient of thermal expansion, making them ideal for ultrafast beam transport applications. These mirrors have a group delay dispersion (GDD) of near zero at their design wavelength range, minimizing dispersion of the reflected beam. TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors are ideal for utilizing the first and second harmonic of Ti:sapphire and Yb:doped lasers for applications such as laser machining and welding.

**Note:** Please [contact us](#) if your application requires a TECHSPEC Low GDD Ultrafast Mirror with a custom wavelength, angle, or size.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).