

8mm 2 MegaPixel Fixed Focal Length Lens



8mm Fixed Focal Length, #14-396

Stock **#14-396** 2 In Stock

-

1

+

C\$568⁴⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$568.40 each
Need More?	Request Quote

Product Downloads

General	
Fixed Focal Length Lens	Type:
Physical & Mechanical Properties	
Variable	Iris Option:
38.50	Length (mm):
32.5	Maximum Diameter (mm):

107	Weight (g):
Optical Properties	
Horizontal Field of View @ Max Sensor Format: 43.8°	
Horizontal Field of View, 1/2" Sensor: 43.8°	
Horizontal Field of View, 1/3" Sensor: 33.4°	
Horizontal Field of View, 1/4" Sensor: 25.36°	
Maximum Image Circle (mm): 8.00	
Focal Length FL (mm): 8.00	
Working Distance (mm): 100 - ∞	
Aperture (f/#): f/1.4 - f/16	
Distortion (%): <-0.7	
Lens Wavelength Range: VIS	
Sensor	
Maximum Sensor Format: 1/2"	
Threading & Mounting	
Filter Thread: M30.5 x 0.50 (Female)	
Mount: C-Mount	
Regulatory Compliance	
Certificate of Conformance: View	

Product Details

- 2 MegaPixel Resolution Design
- Lockable, Manual Focus and Iris
- Fixed Focal Lengths from 4 to 50mm
- C-Mount Lens Mount

2 MegaPixel Fixed Focal Length Lenses are designed for machine vision applications that require higher resolution than the [MegaPixel Fixed Focal Length Lenses](#). These C-Mount lenses feature built-in locking mechanisms for the manual focus and iris, preventing unwanted adjustments. Lenses with a fixed focal length from 4 to 50mm are available with the 6 to 50mm lenses featuring M30.5 x 0.5 filter thread, allowing the use of [machine vision filters](#). 2 MegaPixel Fixed Focal Length Lenses cover ½" and 2/3" sensor sizes, making them compatible with all of our [2MP machine vision cameras](#). These lenses are used in industrial machine vision, [factory automation](#), and factory inspection applications.