

TECHSPEC®

9.0mm Diameter x -27 FL, MgF₂ Coated, Plano-Concave Lens



Stock **#45-383** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

C\$49.00

ADD TO CART

Qty 1-9
C\$49.00
Qty 10+
C\$44.10
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):
-27.00

Substrate: N-SF11
f#: 3.00
Numerical Aperture NA: 0.17
Coating: MgF₂ (400-700nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): -28.68
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 8.1
Coating Specification: R_{avg} ≤1.75% @ 400 - 700nm
Edge Thickness ET (mm): 3.42
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -21.19
Surface Quality: 40-20
Damage Threshold, By Design: 10 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant