

[See all 413 Products in Family](#)

TECHSPEC[®] 9.0mm Dia. x 22.0mm FL, YAG-BBAR, Inked, Plano-Convex Lens



YAG-BBAR Coated Plano-Convex (PCX) Lenses



Stock **#88-814-INK** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

C\$79⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	C\$79.80 each
Qty 10-24	C\$71.40 each
Qty 25-49	C\$64.05 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

Diameter (mm):

9.00 ±0.025	
<1	Centering (arcmin):
1.93 ±0.05	Center Thickness CT (mm):
1.00	Edge Thickness ET (mm):
8.1	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties	
22.00 @ 587.6nm	Effective Focal Length EFL (mm):
20.73	Back Focal Length BFL (mm):
YAG-BBAR (500-1100nm)	Coating:
R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm	Coating Specification:
N-BK7	Substrate: ☐
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
±1	Focal Length Tolerance (%):
11.37	Radius R ₁ (mm):
2.44	f/#:
0.20	Numerical Aperture NA:
500 - 1100	Wavelength Range (nm):
5 J/cm ² @ 532nm, 10ns	Damage Threshold, By Design: ☐

Regulatory Compliance	
View	Certificate of Conformance:

Product Details






- Optimized for R<0.25% @ Both 532nm and 1064nm
- AR Coated to Provide <1.0% Reflectance per Surface for 500 - 1100nm
- Designed for 0° Angle of Incidence
- Various PCX Coating Options: [Uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), and [VIS-EXT](#)

TECHSPEC® YAG-BBAR Coated Plano-Convex (PCX) Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. TECHSPEC® YAG-BBAR Coated Plano-Convex (PCX) Lenses are available in a wide variety of diameters and focal lengths. Identical designs of these PCX lenses are also offered [uncoated](#) or with broadband anti-reflective (BBAR) coatings, which include [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), and [VIS-EXT](#).

Technical Information



N-BK7

Uncoated N-BK7 Typical Transmission <table border="1"><caption>Approximate data for Uncoated N-BK7 Typical Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>350</td><td>70</td></tr><tr><td>400</td><td>92</td></tr><tr><td>600</td><td>92</td></tr><tr><td>800</td><td>92</td></tr><tr><td>1000</td><td>92</td></tr><tr><td>1200</td><td>92</td></tr><tr><td>1400</td><td>92</td></tr><tr><td>1600</td><td>92</td></tr><tr><td>1800</td><td>91</td></tr><tr><td>2000</td><td>90</td></tr><tr><td>2200</td><td>88</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	350	70	400	92	600	92	800	92	1000	92	1200	92	1400	92	1600	92	1800	91	2000	90	2200	88	Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV- NIR spectra. Click Here to Download Data								
Wavelength (nm)	Transmission T (%)																																
350	70																																
400	92																																
600	92																																
800	92																																
1000	92																																
1200	92																																
1400	92																																
1600	92																																
1800	91																																
2000	90																																
2200	88																																
N-BK7 with MgF₂ Coating Typical Transmission <table border="1"><caption>Approximate data for N-BK7 with MgF₂ Coating Typical Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>350</td><td>70</td></tr><tr><td>400</td><td>95</td></tr><tr><td>500</td><td>98</td></tr><tr><td>600</td><td>97</td></tr><tr><td>700</td><td>96</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>94</td></tr><tr><td>1200</td><td>93</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>92</td></tr><tr><td>1800</td><td>91</td></tr><tr><td>2000</td><td>90</td></tr><tr><td>2200</td><td>89</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	350	70	400	95	500	98	600	97	700	96	800	95	1000	94	1200	93	1400	93	1600	92	1800	91	2000	90	2200	89	Typical transmission of a 3mm thick N-BK7 window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data				
Wavelength (nm)	Transmission T (%)																																
350	70																																
400	95																																
500	98																																
600	97																																
700	96																																
800	95																																
1000	94																																
1200	93																																
1400	93																																
1600	92																																
1800	91																																
2000	90																																
2200	89																																
N-BK7 with VIS-EXT Coating Typical Transmission <table border="1"><caption>Approximate data for N-BK7 with VIS-EXT Coating Typical Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>300</td><td>70</td></tr><tr><td>350</td><td>95</td></tr><tr><td>400</td><td>98</td></tr><tr><td>500</td><td>99</td></tr><tr><td>600</td><td>99</td></tr><tr><td>700</td><td>99</td></tr><tr><td>800</td><td>95</td></tr><tr><td>900</td><td>88</td></tr><tr><td>1000</td><td>80</td></tr><tr><td>1100</td><td>75</td></tr><tr><td>1200</td><td>72</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	300	70	350	95	400	98	500	99	600	99	700	99	800	95	900	88	1000	80	1100	75	1200	72	Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data								
Wavelength (nm)	Transmission T (%)																																
300	70																																
350	95																																
400	98																																
500	99																																
600	99																																
700	99																																
800	95																																
900	88																																
1000	80																																
1100	75																																
1200	72																																
N-BK7 with VIS-NIR Coating Typical Transmission <table border="1"><caption>Approximate data for N-BK7 with VIS-NIR Coating Typical Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>350</td><td>70</td></tr><tr><td>400</td><td>98</td></tr><tr><td>500</td><td>97</td></tr><tr><td>600</td><td>99</td></tr><tr><td>700</td><td>97</td></tr><tr><td>800</td><td>99</td></tr><tr><td>900</td><td>98</td></tr><tr><td>1000</td><td>95</td></tr><tr><td>1100</td><td>88</td></tr><tr><td>1200</td><td>80</td></tr><tr><td>1300</td><td>75</td></tr><tr><td>1400</td><td>72</td></tr><tr><td>1500</td><td>70</td></tr><tr><td>1600</td><td>68</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	350	70	400	98	500	97	600	99	700	97	800	99	900	98	1000	95	1100	88	1200	80	1300	75	1400	72	1500	70	1600	68	Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}$ $R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data		
Wavelength (nm)	Transmission T (%)																																
350	70																																
400	98																																
500	97																																
600	99																																
700	97																																
800	99																																
900	98																																
1000	95																																
1100	88																																
1200	80																																
1300	75																																
1400	72																																
1500	70																																
1600	68																																
N-BK7 with VIS 0° Coating Typical Transmission <table border="1"><caption>Approximate data for N-BK7 with VIS 0° Coating Typical Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>350</td><td>70</td></tr><tr><td>400</td><td>95</td></tr><tr><td>425</td><td>98</td></tr><tr><td>500</td><td>99</td></tr><tr><td>600</td><td>99</td></tr><tr><td>675</td><td>99</td></tr><tr><td>800</td><td>95</td></tr><tr><td>900</td><td>88</td></tr><tr><td>1000</td><td>80</td></tr><tr><td>1100</td><td>75</td></tr><tr><td>1200</td><td>72</td></tr><tr><td>1300</td><td>70</td></tr><tr><td>1400</td><td>68</td></tr><tr><td>1500</td><td>65</td></tr><tr><td>1600</td><td>62</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	350	70	400	95	425	98	500	99	600	99	675	99	800	95	900	88	1000	80	1100	75	1200	72	1300	70	1400	68	1500	65	1600	62	Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% \text{ @ } 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																																
350	70																																
400	95																																
425	98																																
500	99																																
600	99																																
675	99																																
800	95																																
900	88																																
1000	80																																
1100	75																																
1200	72																																
1300	70																																
1400	68																																
1500	65																																
1600	62																																

20040060080010001200 Wavelength (nm)		
N-BK7 with YAG-BBAR Coating Typical Transmission T (%) 100 95 90 85 80 75 70 200 400 600 800 1000 1200 1400 1600 Wavelength (nm)		Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\%$ @ 532nm $R_{abs} \leq 0.25\%$ @ 1064nm $R_{avg} \leq 1.0\%$ @ 500 - 1100nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR I Coating Typical Transmission T (%) 100 95 90 85 80 75 70 200 400 600 800 1000 1200 1400 1600 Wavelength (nm)		Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\%$ @ 600 - 1050nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR II Coating Typical Transmission T (%) 100 95 90 85 80 75 70 200 400 600 800 1000 1200 1400 1600 1800 2000 Wavelength (nm)		Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\%$ @ 750 - 800nm $R_{abs} \leq 1.0\%$ @ 800 - 1550nm $R_{avg} \leq 0.7\%$ @ 750 - 1550nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts