

TECHSPEC® 9mm Dia. x 27mm FL, VIS 0° Coated, Achromatic Lens



Stock **#47-654** ☐ **In Stock**
[Other Coating Options](#)

1 **C\$102.20**

ADD TO CART

Qty 1-5
C\$102.20
Qty 6+
C\$81.90
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):
27.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 24.22
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 8.1
Centering (arcmin) : <1
Center Thickness CT (mm) : 5.19 ±0.10
Center Thickness CT 1 (mm) : 3.89 ±0.05
Center Thickness CT 2 (mm) : 1.30 ±0.05
Radius R₁ (mm) : 15.36
Radius R₂ (mm) : -12.01
Radius R₃ (mm) : -39.56
Edge Thickness ET (mm) : 4.26
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 3.00
Numerical Aperture NA : 0.17
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View