

9.5μm 25mm Diameter, IR Shortpass Filter



Stock #21-257 ☐ In Stock

-

1

+

C\$693.00

ADD TO CART

Qty 1-5
C\$693.00
Qty 6+
C\$623.70
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥3.0

Cut-Off Wavelength (nm):

9,500.00
Cut-Off Wavelength (μm): 9.5
Substrate: ☐ Silicon Floatzone
Rejection Wavelength (nm): 10070 - 13800
Surface Quality: 80-50
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.2
Transmission (%): ≥80
Transmission Wavelength (nm): 8000 - 9100
Transmission Wavelength (μm): 8 - 9.1
Type: Shortpass Filter
Durability: ML-C-48497A, Section 4.5.3
Cut-Off Tolerance (%): ±2
Rejection Wavelength (μm): 10.07 - 13.8

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View