

9mm Dia. x 4.5mm FL Protected Aluminum, Concave Mirror



Stock **#43-674** ☐ In Stock

-

1

+

C\$55.30

ADD TO CART

Qty 1-49
C\$55.30
Qty 50+
C\$46.90
Volume Pricing
Request Quote

Get Product Downloads

Substrate: ☐
[N-BK7](#)

Focal Length Tolerance (%):
±2

Surface Quality:
80-50

Diameter (mm):
9.00 ±0.50

Effective Focal Length EFL (mm): 4.50
Radius of Curvature (mm): 9.00
Aperture (f/#): f/0.5
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @400 - 700nm R _{avg} >90% @400 - 2000nm
Coating Type: Metal
Clear Aperture (%): 90
Edge Thickness ET (mm): 3.0
Radius R₁ (mm): 9.00
Thickness Tolerance (mm): ±0.5
Type: Spherical Mirror
Wavelength Range (nm): 400 - 2000

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View