

[See all 14 Products in Family](#)

ACC-01-1106 1 Port AQC107 10GigE Card

See More by [Teledyne FLIR](#)



Teledyne FLIR IIS Forge 5GigE Camera - Front



Stock **#70-308** CLEARANCE **1 In Stock**

- 1 + **C\$299^{.60}**

ADD TO CART

Volume Pricing	
Qty 1+	C\$299.60 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

Regulatory Compliance

[View](#)

Certificate of Conformance:

PRODUCT DETAILS

- Constructed on an All-New Platform
- Offers Burst Mode to Capture Images at Speeds up to 10Gb/s into Memory
- Designed to Simplify OEM Integration with Features Including PoE, Strong Thermal Management and Opto-Isolated Triggering



Teledyne FLIR IIS Forge® 5GigE: The Machine Vision Camera That Fits Anywhere

A 5 Megapixel camera delivering high resolution images at 5GigE speed

The **FLIR IIS Forge® 5GigE** is designed for industrial imaging applications that require high-speed data capture and transfer such as Food, Beverage, Battery, Electronics inspection, and more. Based on the Sony Pregius S Backside Illuminated (BSI) sensors this camera can detect microscopic scratches on various materials due to its higher sensitivity in the UV spectrum. These models support advanced features such as:

- Burst Mode: Achieves 59% faster capture rate at 207 FPS when compared to other 5GigE cameras on the market.
- Lens Shading Correction: Improves entire image uniformity with lenses at a higher F-Stop (removing vignetting).

The **FLIR IIS Forge® 5GigE** features an all-new platform, it is designed to offer the richest combination of on-camera pre-processing features, leverage the industry's most advanced sensors, and support the Trigger-to-Image Reliability (T2IR) framework contributing to robust system designs. Designed to simplify OEM integration with features including PoE, strong thermal management and opto-isolated triggering for streamlined peripherals & easier camera control. Forge® supports both Teledyne Spinnaker and Spera SDKs and GigE Vision compliant software packages.

Features

- Data interface options: 5 GigE, 2.5 GigE, 1 GigE
- 5 Megapixel, 12 Megapixel, 16 Megapixel or 24.5 Megapixel CMOS sensor options
- Color or monochrome models
- 500 MB image buffer for controlled data transfer
- 6-pin GPIO connector
- Compatible with third-party software and hardware
- Support for a wide range of operating systems and host system architectures
- Rich sample code and descriptive API logging
- Simplified product iteration with consistent form factor across sensor sizes

Applications

- Factory automation
 - Biometrics kiosk solutions
 - Bar code reading
 - Container inspection
 - 3D scanning
 - Automated optical inspection
-