

[See all 146 Products in Family](#)

Allied Vision Alvium 1800 U-2050m, 1" 20.2MP, USB 3.0 Monochrome Camera (Board Level)

See More by [Allied Vision](#)



Allied Vision Alvium Camera, Board Level (Front)



Stock #14-901 [CONTACT US](#)

⊖ 1 ⊕ C\$966⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$966.00 each
Need More?	Request Quote

Product Downloads

Monochrome

Spectrum:

General

Monochrome Camera

Type:

Model Number:

1800 U-2050m

Allied Vision **Manufacturer:**

Alvium **Camera Series:**

Physical & Mechanical Properties

13 x 26 x 26 (includes connectors) **Dimensions (mm):**

15 **Weight (g):**

Board Level **Housing:**

Sensor

256KB **Image Buffer:**

1" **Sensor Format:**

20.20 **Resolution (Megapixels):**

17.00 **Frame Rate (fps):**

5,496 x 3,672 **Pixels (H x V):**

2.4 x 2.4 **Pixel Size, H x V (μm):**

13.1 x 8.8 **Sensing Area, H x V (mm):**

Sony IMX183 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Rolling **Shutter Type:**

8/10 bit **Pixel Depth:**

17 μs - 10s **Exposure Time:**

65 **Dynamic Range (dB):**

USB3 Vision v1.0, GenICam **Machine Vision Standard:**

Electrical

3.2 **Power Consumption (W):**

Hardware & Interface Connectivity

USB 3.0 Gen 1 **Interface:**

USB 3.0 Gen 1, Micro-B **Connector:**

Power over USB or via GPIO **Power Supply:**

4 Programmable TTL GPIOs **GPIOs:**

Hardware Trigger (GPIO) or Software Trigger **Synchronization:**

Back Panel **Interface Port Orientation:**

7-pin JST **GPIO Connector Type:**

Threading & Mounting

No Lens Mount **Mount:**

No Mounting Threads/Tripod Adapter **Mounting Threads:**

Environmental & Durability Factors

-20 to +85 (mainboard temperature) **Operating Temperature ($^{\circ}\text{C}$):**

-20 to +85 **Storage Temperature ($^{\circ}\text{C}$):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

Product Details

- Compact, Low Cost, High Performance Design for Machine Vision and Embedded Applications
- ALVIUM® System on Chip (SoC) Technology with Onboard Imaging Preprocessing
- Up to 24.60 MegaPixels, 1.2" Sensor Format
- [Allied Vision Alvium Right Angle USB 3.1 Cameras](#) Also Available

Allied Vision Alvium USB 3.0 Cameras feature a lightweight compact form factor with ALVIUM® System on Chip (SoC) technology, offering a comprehensive image processing library for advanced onboard image correction and preprocessing functions to relieve host computer and processor workload. In addition to smart camera operations, the unique SoC design also allows for low power consumption and ease of integration, making them ideal for next generation machine vision, robotics and embedded vision applications. The cameras feature a variety of popular Sony Pregius and On Semi CMOS sensors with high image quality, fast frame rate and USB3 Vision interface standard. The actively aligned lens mount minimizes inconsistency and variation. Allied Vision Alvium USB 3.0 Cameras feature a USB port on the back panel and are available in a variety of monochrome, color, and NIR configurations, including C-Mount, CS-Mount, and S-Mount. Full housing versions are best suited for prototyping, development and end user uses. Partial housing and board level configurations have exposed image sensor PCB without heat sinks to reduce space and facilitate system integration making them ideal for OEM embedded design.

Note: Board level versions do not have a lens mount.

Calibration Services