

TECHSPEC®

9mm Dia. x 9mm FL Uncoated, Double-Convex Lens



Stock **#32-018** ☐ **In Stock**
☐ [Other Coating Options](#)

-

1

+

C\$41.30

ADD TO CART

Qty 1-9
C\$41.30
Qty 10+
C\$37.10
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Back Focal Length BFL (mm):
7.90

Effective Focal Length EFL (mm): 9.00
Coating: Uncoated
Substrate: 
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <3
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.45
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.60
Radius R₁=R₂ (mm): 11.38
Clear Aperture CA (mm): 8.1
f/#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 380 - 2500

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant