

TECHSPEC® 9mm Dia. x -9mm FL, VIS 0° Coated, Double-Concave Lens



Stock **#48-344** ☐ In Stock
[Other Coating Options](#)

1 **C\$55.30**

ADD TO CART

Qty 1-9
C\$55.30
Qty 10+
C\$49.70
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):
-9.00

Substrate: N-SF11
f/#: 1.00
Numerical Aperture NA: 0.50
Coating: VS 0° (425-675nm)
Type: Double-Concave Lens
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): -9.61
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.25
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <3
Clear Aperture CA (mm): 8.1
Coating Specification: R_{avg} ≤0.4% @ 425 - 675nm
Edge Thickness ET (mm): 3.48
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -14.60
Surface Quality: 40-20
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant