


TECHSPEC[®] Elliptical Mirror, 26.97mm Minor Axis, 400 - 700nm



Stock **#72-944** 7 In Stock

-

1

+

C\$187^{.60}

ADD TO CART

Volume Pricing	
Qty 1-5	C\$187.60 each
Qty 6+	C\$149.80 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Flat Mirror

Type:

Flatness specification is Peak to Valley

Note:

Physical & Mechanical Properties	
±0.030	Thickness Tolerance (inches):
6.35 ±0.76	Thickness (mm):
24.28 (Minor Axis) 34.34 (Major Axis)	Clear Aperture CA (mm):
±0.015	Dimensional Tolerance (inches):
±0.38	Dimensional Tolerance (mm):
38.15	Major Axis (mm):
26.97	Minor Axis (mm):
Optical Properties	
Dielectric	Coating Type:
Dielectric Mirror (400-750nm)	Coating:
λ/8	Surface Flatness (P-V):
400 - 750	Wavelength Range (nm):
BOROFLOAT®	Substrate: ☐
R _{avg} >98% @ 400 - 750nm (0 - 45°) R _{avg} >99% @ 400 - 750nm (0°)	Coating Specification:
60-40	Surface Quality:
0.5 J/cm² @ 532nm, 20ns, 20Hz	Damage Threshold, By Design: ☐
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Circular Profile When Oriented at 45°
 - Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
 - Enhanced Reflectivity and LIDT over Metallic Coatings
- TECHSPEC® Broadband Dielectric Elliptical Flat Mirrors are ideal for research and astronomical applications. Because of their elongated major axis, they are suited to bending and folding light at precise angles with minimum wavefront distortion. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. TECHSPEC® Broadband Dielectric Elliptical Flat Mirrors feature a BOROFLOAT® substrate and are available with minor axes up to 76.20mm and major axes up to 107.77mm