

Allied Vision Prosilica GC750 1/3" CCD GigE Monochrome Camera

See More by [Allied Vision](#)



Stock **#63-421** [CONTACT US](#)

- 1 +

C\$1,044.40

ADD TO CART

Qty 1+
C\$1,044.40

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE

Type:
Monochrome Camera

Manufacturer:
Allied Vision

Mounting Threads: ¼-20 with Tripod Mount Adapter #63-432
Image Buffer: 64MB
Camera Family: Prosilica GC
Model Number: GC750
Imaging Sensor: ON Semi MT9V022
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/3"
Resolution (MegaPixels): 0.30
Pixels (H x V): 752 x 480
Pixel Size, H x V (µm): 6 x 6
Sensing Area, H x V (mm): 4.6 x 3.0
Frame Rate (fps): 60.00
Pixel Depth: 10 bit
Exposure Time: 30µs - 1s
Connector: GigE, RJ45
Power Supply: Power Supply Required and Sold Separately. USA: #15-281 Europe: #15-281 Japan: #15-281 China: #15-281
Power Consumption (W): 2.2 (12VDC External Power Supply)
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 1 non-isolated input, 1 non-isolated output
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 45.7 x 33.9 x 33 (excludes connectors and lens mount)
Weight (g): 85
Mount: CS-Mount
Housing: Full
Interface Port Orientation: Back Panel
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -10 to +70
GPIO Connector Type: 12-pin Hirose (HR10)
Machine Vision Standard: GigE Vision v1.2, GenICam SFNC V1.2.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant