

[See all 127 Products in Family](#)

Allied Vision Alvium 1800 U-500c, 1/2.5" 5.0MP, Right Angle USB 3.1 Color Camera (Board Level)

See More by [Allied Vision](#)



Allied Vision Alvium Camera, Board Level, Right Angle IO Port (Front)



Stock **#14-153** [CONTACT US](#)

[Similar Cameras](#)

1 **C\$450⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	C\$450.80 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Color

Spectrum:

General

Type:

Color Camera

1800 U-500c

Model Number:

Allied Vision

Manufacturer:

Alvium Right Angle

Camera Series:

Physical & Mechanical Properties

Dimensions (mm):
13 x 30 x 26 (includes connectors and lens mount)

Weight (g):
15

Housing:
Board Level

Sensor

Image Buffer:
256KB

Sensor Format:
1/2.5"

Resolution (Megapixels):
5.00

Frame Rate (fps):
67.00

Pixels (H x V):
2,592 x 1,944

Pixel Size, H x V (µm):
2.2 x 2.2

Sensing Area, H x V (mm):
5.7 x 4.3

Imaging Sensor:
ON Semi AR0521

Type of Sensor:
Progressive Scan CMOS

Shutter Type:
Rolling

Pixel Depth:
8/10 bit

Exposure Time:
13µs - 849ms

Dynamic Range (dB):
Not Specified

Machine Vision Standard:
USB3 Vision v1.0, GenICam

Electrical

Power Consumption (W):
2.2

Hardware & Interface Connectivity

Interface:
USB 3.1 Gen 1

Connector:
USB 3.1 Gen 1, Micro-B

Power Supply:
Power over USB or via GPIO

GPIOs:
4 Programmable TTL GPIOs

Synchronization:
Hardware Trigger (GPIO) or Software Trigger

Interface Port Orientation:
Back Panel (Right Angle)

GPIO Connector Type:
7-pin JST

Threading & Mounting

Mount:
No Lens Mount

Mounting Threads:
No Mounting Threads/Tripod Adapter

Environmental & Durability Factors

Operating Temperature (°C):
+5 to +80

-10 to +70

Storage Temperature (°C):

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 240:

Product Details

- Right Angle USB Port Orientation
- Compact, Low Cost, High Performance Design for Machine Vision and Embedded Applications
- ALVIUM® System on Chip (SoC) Technology with Onboard Imaging Preprocessing
- [Allied Vision Alvium USB 3.1 Cameras](#) Also Available

Allied Vision Alvium Right Angle USB 3.1 Cameras feature ALVIUM® System on Chip (SoC) technology and a right-angle USB port in a lightweight compact form factor, offering a comprehensive image processing library for advanced onboard image correction, preprocessing functions to relieve host computer and processor workload, and allow for easy system integration. In addition to smart camera operations, the unique SoC design also allows for low power consumption and ease of integration, making them ideal for next generation machine vision, robotics and embedded vision applications. The cameras feature a variety of popular Sony Pregius and On Semi CMOS sensors with high image quality, fast frame rate and USB3 Vision interface standard. The actively aligned lens mount minimizes inconsistency and variation. Allied Vision Alvium Right Angle USB 3.1 Cameras feature a 90° right angle USB port and are available in a variety of monochrome, color, and NIR configurations, including C-Mount, CS-Mount, and S-Mount. Full housing versions are best suited for prototyping, development and end user uses. Partial housing and board level configurations have exposed image sensor PCB without heat sinks to reduce space and facilitate system integration making them ideal for OEM embedded design.

Note: Board level versions do not have a lens mount.

Calibration Services
