

BeamR2-Si Scanning Slit Beam Profiler



#24-215 DataRay Scanning Slit Beam Profiler

Stock **#24-215** 1 In Stock

-

1

+

C\$7,168⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$7,168.00 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
60.96 x 67.31 x 66.17	Dimensions (mm):
±1µm	Dimensional Accuracy:
Optical Properties	
190 - 1150	Spectral Range:
2µm to 4mm	Beam Diameter (µm):

Sensor	
5Hz	Frame Rate:
Electrical	
1,000:1	Signal to Noise S/N Ratio (dB):
1 W Total & 0.5 mW/μm²	Maximum Power (W):
Threading & Mounting	
1/4-20 thread	Mount:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Designed For Use From 190 to 1150nm
- Measure Beam Diameters of 2μm to 4mm
- Robust Easy to Use Software Provided

DataRay Scanning Slit Beam Profilers feature a silicon detector making it perfect for a 190 to 1150nm spectral range. Equipped with 2.5μm slits and larger knife-edge slits, the Beam'R2 is capable of measuring beams with diameters down to 2μm. Scanning slit instruments offer much higher resolution than camera-based systems, and are compatible with both continuous wave and pulsed laser sources. DataRay Scanning Slit Beam Profilers are ideal for optical assembly and instrument alignment, real-time diagnosis of focusing and alignment errors, real-time setting of multiple assemblies to the same focus. These profilers are USB 2.0 powered and include a 3m USB 2.0 cable.