

[See all 7 Products in Family](#)

Chiron Series 3mm Aperture (Recertified 05-P)




Photo shows part 29674

Stock **#29-674-RCD-05P** RECERTIFIED **1 In Stock**

- 1 + **C\$7,392⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	C\$7,392.00 each
Need More?	Request Quote

Product Downloads

General

Chiron Series	Type:
BBO	Crystal Type:

Physical & Mechanical Properties

3	Aperture Diameter (mm):
---	-------------------------

Optical Properties

200 - 1650	Wavelength Range (nm):
<N6	Single Pass Distortion @ 1064 nm:
> 1000:1	Intrinsic Contrast Ratio (ICR) @ 1064 nm:
< 1.5%	Single Pass Insertion Loss:
Electrical	
> 1000:1	Voltage Contrast Ratio (VCR) @ 1064 nm:
1000	Repetition Rate (kHz):
Hardware & Interface Connectivity	
#29-678	Power Supply:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- High Performance Phase Modulation up to 1MHz
- >98% Transmission from UV to NIR Spectra
- >10 J/cm² Damage Threshold
- Ideal for Q-switching, Pulse Picking, and Laser Power Control

G&H Pockels Cells are designed to provide high performance electro-optic phase modulation through the [Pockels effect](#), serving as a voltage controlled waveplate. Utilizing the highest purity 99% KD*P crystals or triple Beta Barium Borate (BBO) crystals, these Pockels cells achieve >98% transmission from the UV to NIR spectra and feature a high damage threshold of >10 J/cm². The sealed, nitrogen-filled, compact design of these Pockels cells with ceramic apertures and premium UV-grade fused silica windows ensures high transmission and contrast ratios over its long lifetime. The Impact Series features robust sol-gel and dielectric AR coatings with high damage thresholds compatible with common laser wavelengths from 300 – 1100nm. Advanced connectors designed for high-voltage operations offer rapid connection which facilitates straightforward system design and assembly. Chiron Pockels cells minimize piezoelectric coupling coefficients and the BBO crystal enables them to operate at high repetition rates reaching up to 1 MHz, devoid of any piezoelectric ringing. Additionally, leveraging the dual crystal configuration of BBO, the Chiron series achieves a reduced driving quarter wave voltage, while upholding a voltage contrast ratio exceeding 1000:1 at 1064nm. These Pockels cells are ideal for a range of laser-based applications such as Q-switching, pulse picking, regenerative amplification, and laser power control.