

# CM3-U3-50S5M-CS 2/3" Chameleon®3 Monochrome Camera

See More by [Teledyne FLIR](#)



USB 3.0 FLIR Chameleon Camera



Stock #36-077 **1 In Stock**

⊖ 1 ⊕ C\$1,246<sup>00</sup>

**ADD TO CART**

Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | C\$1,246.00 each              |
| Need More? | <a href="#">Request Quote</a> |

Product Downloads

Monochrome **Spectrum:**

**General**

Monochrome Camera **Type:**

CM3-U3-50S5M-CS **Model Number:**

**Manufacturer:**

FLIR

Camera Series:

Chameleon@3

## Physical & Mechanical Properties

Dimensions (mm):

44 x 35 x 22.1 (excludes connectors and lens mount)

Weight (g):

54.9

Housing:

Full

## Sensor

Image Buffer:

16MB

Sensor Format:

2/3"

Resolution (Megapixels):

5.00

Frame Rate (fps):

35.00

Pixels (H x V):

2,448 x 2,048

Pixel Size, H x V (µm):

3.45 x 3.45

Sensing Area, H x V (mm):

8.45 x 7.07

Imaging Sensor:

Sony IMX264

Type of Sensor:

Progressive Scan CMOS

Shutter Type:

Global

Pixel Depth:

12 bit

Exposure Time:

13µs - 31.995s

Dynamic Range (dB):

70.97

Machine Vision Standard:

USB3 Vision v1.0

## Electrical

Power Consumption (W):

Not Specified

## Hardware & Interface Connectivity

Interface:

USB 3.1 Gen 1

Connector:

USB 3.1 Gen 1, Micro-B with Screw Locks

Power Supply:

Power over USB or via GPIO

GPIOs:

1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports

Synchronization:

Hardware Trigger (GPIO)

Interface Port Orientation:

Side Panel

GPIO Connector Type:

9-pin JST

## Threading & Mounting

Mount:

CS-Mount

Mounting Threads:

1/4-20 with Tripod Mount Adapter [#88-210](#)

## Environmental & Durability Factors

Operating Temperature (°C):

0 to +45

Storage Temperature (°C):

-30 to +60

[View](#)

## Product Details

- USB3 Connectivity
- Lightweight Construction
- Compact Design



Teledyne  
Authorized  
Distributor

### Teledyne FLIR IIS Chameleon@3: Easy integration with USB3

Compact USB3 cameras

The **Chameleon@3** camera line combines popular CCD and CMOS image sensors with the ease of use of USB 3.0, with a compact form factor and camera sensor resolutions ranging from 1.3 MP to 5.0 MP.

These cameras feature a compact 44 x 35 x 19.5mm lightweight metal case designed for reliability. They offer multiple mounting points and a locking USB 3.0 connection. The camera includes an on-camera frame buffer for image retransmission and an optoisolated GPIO with a locking connection.

#### Features

- Compact form factor
- On-camera image processing: color interpolation, gamma, & LUT
- Data interface: USB3
- 16 MByte frame buffer
- LED Status indicator
- Spinnaker SDK and FlyCapture interfaces

#### Applications

- Life science instrumentation
- Factory automation
- Biometrics kiosk solutions
- Ophthalmoscopy
- 3D scanning
- Automated optical inspection