

[See all 1 Products in Family](#)

Coherent® PowerMax Wand 1299161 | 325 - 1065nm

See More by [Coherent®](#)



Stock #88-425 **7 In Stock**

⊖ 1 ⊕ C\$2,905⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,905.00 each
Need More?	Request Quote

Product Downloads

General

Diffuse Quartz	Type of Optics:
±1	Linearity (%):
±1	Calibration Uncertainty (%):
Air	Cooling Method:
0.5	Response Time (s):

Physical & Mechanical Properties

8
Active Area Diameter (mm):

Optical Properties

514
Calibration Wavelength (nm):

325 - 1065
Wavelength Range (nm):

Sensor

Silicon
Type of Sensor:

Electrical

±4 (325 - 900nm)
±5 (900 - 1065nm)
Spectral Compensation Accuracy (%):

20
Maximum Incident Power Density (W/cm²):

8.5µW - 140mW
Power Range:

170nW
Noise Equivalent Power:

Hardware & Interface Connectivity

2.5
Length of Cable (m):

USB
Computer Interface:

Regulatory Compliance

Exempt
RoHS 2015:

Contains SVHC(s)
Reach 224:

View
Certificate of Conformance:

Product Details

- High Sensitivity Silicon Photodiode
- Slim Profile
- Ideal for CW or Pulsed Laser Measurements

The Coherent® PowerMax Wand utilizes a high-sensitivity silicon photodiode for continuous wave or pulsed laser measurement from the ultraviolet to the infrared. The Coherent PowerMax Wand is ideal for power measurements from 8.5µW to over 140mW depending on the laser wavelength, and for pulsed lasers greater than 50pps. This USB-powered laser measurement device utilizes spectrally calibrated filters to attenuate the laser beam, allowing for a higher average power measurement than is typically possible with a photodiode.