

[See all 15 Products in Family](#)

Coherent® EnergyMax 1110573 | 1000μJ-2000mJ, DB25

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#12-388** [CONTACT US](#)

-

1

+

C\$2,730^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,730.00 each
Need More?	Request Quote

Product Downloads

General	
Model Number:	
J-50MB-HE Coherent Part Number: 1110573	
Type:	
Meter required	
Linearity (%):	
±3	
Calibration Uncertainty (%):	
±2	

<33	Noise Equivalent Energy (μJ):
	Compatible Meters:
#88-412 or #35-203	

Maximum Incident Energy Density: 500mJ/cm ² (10ns, 1064nm)	
1mJ - 2J	Energy Range:
	Preferred Meter:
#66-277	

Physical & Mechanical Properties

Active Area Diameter (mm):	
50	

Optical Properties

Calibration Wavelength (nm):	
1064	
Maximum Pulse Width (μs):	
57	
Wavelength Range (nm):	
190 - 12000	

Sensor

Type of Sensor:	
Pyroelectric	

Electrical

Maximum Repetition Rate (pps):	
300	
Maximum Incident Beam Power (W):	
10	

Hardware & Interface Connectivity

Connector:	
DB25	
Length of Cable (m):	
2.5	

Regulatory Compliance

RoHS 2015:	
Exempt	
Reach 224:	
Contains SVHC(s)	
Certificate of Conformance:	
View	

Product Details

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.