

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Life Science Lasers](#)  
/ [Coherent® High Performance OBIS™ LX/LS Laser Systems](#)

[« See all 58 Products in Family](#)

# Coherent® OBIS™ 1261779 | 532nm LS 50mW Laser

See More by [Coherent®](#)

Stock #12-344 [CONTACT US](#)



-

 1 

+

**C\$9,137<sup>.80</sup>**

ADD TO CART



| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | C\$9,137.80 each              |
| Need More?     | <a href="#">Request Quote</a> |

| Product Downloads  |                 |
|--------------------|-----------------|
| Start Up Guide:pdf |                 |
| STEP:step          | PDF Drawing:pdf |
| IGES:igs           | Spec Sheets:pdf |
| User Manual:pdf    | Software        |
| eDrawing:eprt      |                 |
| EO Spec Sheet      |                 |

**Note:** This item requires accessories for use | [Learn More](#)

| General                          |  |                        |                                             |
|----------------------------------|--|------------------------|---------------------------------------------|
| Warm-Up Time (minutes):          |  | <5                     | Manufacturer: Coherent®                     |
| Type of Laser:                   |  | Diode                  | Laser Class - CDRH: IIIb                    |
| Model Number:                    |  | 1261779                |                                             |
| Physical & Mechanical Properties |  |                        |                                             |
| Pointing Stability (µrad/°C):    |  | <5                     | Pointing Stability (µrad): <30              |
| Optical Properties               |  |                        |                                             |
| Polarization:                    |  | 100:1                  | Spatial Mode: TEM <sub>00</sub>             |
| Wavelength (nm):                 |  | 532.00 ±2              | Mode Quality, M <sup>2</sup> : ≤1.1         |
| Beam Diameter Tolerance (mm):    |  | ±0.05                  | Beam Diameter (mm): 0.7                     |
| Beam Divergence (mrad):          |  | Full-Angle: ≤1.2       | Color: Green                                |
| Electrical                       |  |                        |                                             |
| Output Power (mW):               |  | 50                     | Power Stability (%): <2                     |
| Modulation Frequency (MHz):      |  | Max Digital: 0.05      | Modulation Frequency (kHz): Max Analog: 100 |
| RMS Noise:                       |  | ≤0.25% (20Hz to 20MHz) |                                             |

| Hardware & Interface Connectivity |                                                                                                                                                                        |
|-----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Power Supply:</b>              | Power Supply Required and Sold Separately:<br>USA: <b>#87-473</b><br>Europe: <b>#87-473</b><br>Japan: <b>#87-473</b><br>Korea: <b>#87-473</b><br>China: <b>#87-473</b> |
| <b>Output Type:</b>               | Free Space                                                                                                                                                             |

| Environmental & Durability Factors |          |
|------------------------------------|----------|
| <b>Operating Temperature (°C):</b> | 15 to 40 |

| Regulatory Compliance              |                         |
|------------------------------------|-------------------------|
| <b>RoHS 2015:</b>                  | <b>Exempt</b>           |
| <b>Certificate of Conformance:</b> | <b>View</b>             |
| <b>Reach 224:</b>                  | <b>Contains SVHC(s)</b> |

## Product Details

- Same Compact Design for All Wavelength Options
- Integrated Control Electronics with Analog and Digital Modulation
- Circular Beam with Superior Beam Quality
- **Coherent® High Performance OBIS™ LX/LS Fiber-Pigtailed Laser Systems** Also Available

Coherent® High Performance OBIS™ LX/LS Laser Systems are compact, plug-and-play lasers that offer a wide range of wavelengths from the ultraviolet to the near-infrared in a single platform. Although each laser utilizes one of two technologies, either Coherent’s proprietary Optically Pumped Semiconductor Laser (OPSL) or laser diode-based, these laser systems feature the same beam parameters in packages that allow the user to plug-and-play alternate wavelengths as needed. Coherent® High Performance OBIS™ LX/LS Laser Systems includes a USB, RS-485, and full I/O interface. A multicolor LED has been integrated into the top cover to provide laser status at a glance.

**OBIS Laser System Startup Guide**

This downloadable PDF provides guidance on interfacing with OBIS controllers and power supplies, mounting and connecting the heatsink, and starting modulation.

[Download Startup Guide](#)

**Note:** A power supply is required for operation and sold separately. OBIS remote is required for CDRH certified systems. The OBIS heat sink is recommended.

Three power supply options are available, but only one is required. **#87-472** (not CDRH certified) includes a power supply with power cord. **#87-473** (CDRH certified) includes a 1m laser-to-remote cable, and DC power supply with power cable. **#87-475** (CDRH certified) includes a 6 laser scientific remote, internal power supply, and six 1m laser-to-remote cables with power cord.

Coherent® High Performance OBIS™ LX/LS Laser Systems are designed for an extensive range of OEM or scientific applications including environmental monitoring, inspection, or machine vision, or for use in the life sciences for the fluorescence excitation of dyes and proteins in flow cytometry, microscopy, DNA sequencing, polymerase chain reaction (PCR) diagnostic instruments, or drug delivery. These lasers feature smart electronics to ensure superior low-noise optical performance, and an ultra-small controller that has been integrated into the laser head.

## Technical Information

## Accessories

**Note:** Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

|       | Title                                                                      | Compare | Stock Number | Price                        | Buy            |
|-------|----------------------------------------------------------------------------|---------|--------------|------------------------------|----------------|
| MORE+ | 3m OBIS Laser-to-Remote Cable                                              |         | #11-504      | C\$336.00<br>Request Quote   | CONTACT US 1   |
| MORE+ | Coherent® OBIS™ LX/LS Laser Box with Power Supply 1228877                  |         | #33-351      | C\$4,487.00<br>Request Quote | 2 In Stock 1   |
| MORE+ | Coherent® OBIS™ 1214874   DC Power Supply and Power Cord (Non-CDRH)        |         | #87-472      | C\$126.00<br>Request Quote   | 5 In Stock 1   |
| MORE+ | Heat Sink for OBIS™ Laser                                                  |         | #34-249      | C\$333.20<br>Request Quote   | 20+ In Stock 1 |
| MORE+ | Coherent® OBIS™ 1214875   Remote w/ DC Power Supply & Power Cord (CDRH)    |         | #87-473      | C\$889.00<br>Request Quote   | CONTACT US 1   |
| MORE+ | Coherent® OBIS™ 1234466   6 Laser Scientific Remote w/ Power Supply (CDRH) |         | #87-475      | C\$3,437.00<br>Request Quote | 1 In Stock 1   |
| MORE+ | Coherent® OBIS™ 1193289   Heat Sink w/ Integrated Cooling Fan              |         | #87-474      | C\$595.00<br>Request Quote   | 2 In Stock 1   |

Related Products



Laser Safety Glasses and Goggles



Laser Measurement and Electronics




Laser Mirrors



Bandpass Filters

Frequently Purchased Together



#34-249 - Heat Sink for OBIS™ Laser  
C\$333.20

Qty



#86-952 - 575nm CWL, 25mm Dia. Hard Coated OD 4.0 50nm Bandpass Filter  
C\$392.00

Qty



#86-954 - 675nm CWL, 25mm Dia. Hard Coated OD 4.0 50nm Bandpass Filter  
C\$392.00

Qty



#87-473 - Coherent® OBIS™ 1214875 | Remote w/ DC Power Supply & Power Cord (CDRH)  
C\$889.00

Qty

Resources

Media Type

TECHNICAL TOOL

APPLICATION NOTE

APPLICATION NOTE

Common Laser Types

- ☐ Technical Tool
- ☐ Application Note
- ☐ Video
- ☐ FAQ
- ☐ Glossary
- ☐ Published Article
- ☐ Scientific Paper

Gaussian Beams Calculator

Gaussian Beam Propagation

▶ VIDEO

Understanding Lasers and How They're Used Every...

? FAQ

Can a laser beam be seen from the side?

? FAQ

What factors are involved in how well I can see a laser...

View More