

Coherent® OBIS™ FP 1219477 | 488nm LX 100mW Laser, Fiber Pigtail, FC

See More by [Coherent®](#)



Coherent® High Performance OBIS™ Fiber-Pigtailed Laser Systems



Stock #12-365 [CONTACT US](#)

1 **C\$15,064⁰⁰**

ADD TO CART

Volume Pricing

Qty 1+	C\$15,064.00 each
Need More?	Request Quote

Product Downloads



General

<5	Warm-Up Time (minutes):
3mm Mono-Coil	Fiber Cable Type:
Coherent®	Manufacturer:
	Type of Laser:

Diode	
IIIb	Laser Class - CDRH:
1219477	Model Number:
Optical Properties	
100:1	Polarization:
TEM ₀₀	Spatial Mode:
488.00 ±5	Wavelength (nm):
≤1.1	Mode Quality, M²:
Blue	Color:
0.05	Fiber Numerical Aperture NA (1/e²):
Electrical	
100	Output Power (mW):
<2	Power Stability (%):
Digital: 150	Modulation Frequency (MHz):
Analog: 500	Modulation Frequency (kHz):
≤0.2% (20Hz to 20MHz)	RMS Noise:
Hardware & Interface Connectivity	
Power Supply Required and Sold Separately. USA: #87-473 Europe: #87-473 Japan: #87-473 Korea: #87-473 China: #87-473	Power Supply:
FC/APC; 8° angled	Output from Fiber:
Fiber-Coupled	Output Type:
Environmental & Durability Factors	
10 to 50	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- High Performance OBIS™ LX/LS Lasers with Added Fiber Optic Capability
- Permanent Fiber Attachment Extends Lifetime with Guaranteed Power
- Single-Mode Polarization-Maintaining Fiber with an FC/APC Connector Provide High-Quality and Low-Noise Laser Beam Output
- [Coherent® High Performance OBIS™ LX/LS Laser Systems](#) Also Available

Coherent® High Performance OBIS™ LX/LS Fiber-Pigtailed Laser Systems are plug-and-play lasers available in wavelengths from the ultraviolet to the near-infrared with an added fiber attachment. The fiber optic is permanently attached to the laser, providing an extended lifetime of the fiber and guaranteed power consistency. An FC/APC connector terminates the fiber to enable connections to other systems without concern for high noise interference. Coherent® High Performance OBIS™ LX/LS Fiber-Pigtailed Laser Systems produce high-quality, low-noise laser beams and also allow for hands-free operation. These fiber-pigtailed lasers are used in confocal microscopy, DNA sequencing, polymerase chain reaction (PCR) diagnostic instruments, flow cytometry, medical imaging, and instrumentation applications.

OBIS Laser System Startup Guide

This downloadable PDF provides guidance on interfacing with OBIS controllers and power supplies, mounting and connecting the heatsink, and starting modulation.

[Download Startup Guide](#)