

Coherent® PowerMax USB PM30 Measurement System 1174257 | 10mW-30W

See More by [Coherent®](#)



Stock #12-410 [CONTACT US](#)

- 1 + C\$2,618⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$2,618.00 each
Need More?	Request Quote

Product Downloads

General

Model Number:
PM30
Coherent Part Number: 1174257

Type:
Meterless

Calibration Uncertainty (%):
±2

Long Pulse Joule Mode Range (J):

Cooling Method:

Air

Maximum Incident Energy Density (J/cm²):

0.6 @ 1064nm, 10ns

Physical & Mechanical Properties**Active Area Diameter (mm):**

19

Optical Properties**Calibration Wavelength (nm):**

10600

Wavelength Range (nm):

190 - 11000

Wavelength Range (μm):

0.19 - 11

Sensor**Type of Sensor:**

Thermopile

Electrical**Spectral Compensation Accuracy (%):**

±1.5

Maximum Intermittent Power, <5min (W):

50 (air-cooled)

Maximum Incident Power Density (kW/cm²):

6

Power Range:

10mW - 30W

Hardware & Interface Connectivity**Length of Cable (m):**

2.5

Computer Interface:

USB

Regulatory Compliance**RoHS 2015:**[Exempt](#)**Reach 224:**[Contains SVHC\(s\)](#)**Certificate of Conformance:**[View](#)

Product Details

- Superior Damage Resistance
- Wide Dynamic Range
- ISO 17025 Certified

Coherent® Thermopile Power Sensors are ideal for measuring the average power of continuous wave lasers or pulsed laser energy. Thermopile sensors operate by absorbing and converting incident laser radiation into heat, which then flows to a heat sink. The temperature difference between the absorber and heat sink is converted into an electrical signal by a thermocouple junction. Coherent® Thermopile Power Sensors, unlike semiconductor sensors, do not saturate. Unlike semiconductor sensors, thermopile sensors feature high power capability and flat spectral response.