

[See all 4 Products in Family](#)

## Dual Axis Linear Scale Micrometer on Opal Glass



Stock **#58-763** **1 In Stock**

⊖ 1 ⊕ C\$1,092.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	C\$1,092.00 each
Qty 5+	C\$1,037.82 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

No **NIST Certification:**

#### Physical & Mechanical Properties

Metric: 25µm  
English: 1 mil (0.001") **Scale Divisions:**

25.4 x 76.2 **Dimensions (mm):**

**Thickness (mm):**

1.50 ±0.100

Dimensional Tolerance (mm):

±0.100

## Optical Properties

Chrome on Opal Glass

Substrate:

## Regulatory Compliance

Compliant

RoHS 2015:

[View](#)

Certificate of Conformance:

Compliant

Reach 235:

## Product Details

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

## Technical Information

