


Dual Axis Linear Scale Micrometer on Opal Glass



Stock **#58-763** **1 In Stock**

-

1

+

C\$1,092^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$1,092.00 each
Qty 5+	C\$1,037.82 each
Need More?	Request Quote

Product Downloads

General

No

NIST Certification:

Physical & Mechanical Properties

Metric: 25µm
English: 1 mil (0.001")

Scale Divisions:

25.4 x 76.2

Dimensions (mm):

Thickness (mm):

1.50 ±0.100	
±0.100	Dimensional Tolerance (mm):
Optical Properties	
Chrome on Opal Glass	Substrate:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

Technical Information

