

Dual Axis Linear Scale Micrometer w/ NIST Certificate



Stock **#59-276** 2 In Stock

-

1

+

C\$1,624^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$1,624.00 each
Qty 5+	C\$1,544.06 each
Need More?	Request Quote

Product Downloads

General

NIST Certification:

Yes

Physical & Mechanical Properties

Scale Divisions:

Metric: 25µm
English: 1 mil (0.001")

Dimensions (mm):

25.4 x 76.2

Thickness (mm):

1.50 ±0.100	Dimensional Tolerance (mm):	
±0.100		
Optical Properties		
Chrome on Glass	Substrate:	
60-40	Surface Quality:	
Regulatory Compliance		
Compliant	RoHS 2015:	
View	Certificate of Conformance:	
Compliant	Reach 235:	

Product Details

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

Technical Information

