

Two circular optical filters are shown against a dark background. The filter on the left has a blue-tinted center and is labeled '8395/870-22.8'. The filter on the right has a yellow-tinted center and is labeled '850/850-22.8'. Both filters have a black outer ring with the text in white.

 1 **C\$190**^{.40}

[ADD TO CART](#)

Volume Pricing	
Qty 1+	C\$190.40 each
Need More?	Request Quote

Product Downloads

Full Width-Half Max FWHM Range (nm):
250nm, 50nm $\pm$ 20 nm VIS, $\pm$ 10 nm NIR

General	
---------	--

Type: Dual Bandpass Mounted Imaging Filter

Model Number: DB850-30.5

Physical & Mechanical Properties

Outer Diameter (mm): 32.5

Substrate Thickness (mm):

2mm	
Optical Properties	
Color:	VIS-850nm-NIR
Surface Quality:	40/20
Transmission (%):	≥90%
Transmission Wavelength (nm):	404-645nm, 835-875nm
Threading & Mounting	
Filter Thread:	M30.5 x 0.50
Mount Thickness (mm):	5.2
Regulatory Compliance	
Certificate of Conformance:	View

Product Details

- Block and Transmit Desired Key VIS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (VIS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

Note: Other filter threads are available upon request.