

## DUV Waveplate $\lambda/2$ 266nm 12.7mm Dia



Stock #29-968 **6 In Stock**

- 1 + C\$714.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-5	C\$714.00 each
Qty 6+	C\$555.80 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Crystalline Waveplate **Type:**

Air spaced; no mounting glue; no glue contacted spacer between crystals **Configuration:**

#### Physical & Mechanical Properties

>7 **Clear Aperture CA (mm):**

**Diameter (mm):**

12.70 +0.00/-0.25

6.00 **Thickness (mm):**

Crystalline **Construction:**

<3 **Parallelism (arcsec):**

## Optical Properties

Laser V-Coat (266nm) **Coating:**

266 **Design Wavelength DWL (nm):**

Crystal Quartz **Substrate:**

$\lambda/2$  **Retardance:**

10-5 **Surface Quality:**

$\lambda/10$  @632.8nm **Transmitted Wavefront, P-V:**

$\pm\lambda/100$  @20°C **Retardance Tolerance:**

0.0001 **Temperature Coefficient ( $\lambda$ /°C):**

R<0.2% @266nm **Coating Specification:**

0 **Retardance Order:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

## Product Details

- 257nm and 266nm Deep UV Wavelengths Available
- Ideal For Vacuum Compatible Applications
- Non-Anodized Mount and Adhesive-Free Construction

DUV Vacuum-Compatible Waveplates are mounted in an unanodized aluminum housing and feature adhesive-free construction for low outgassing in vacuum environments. These waveplates are optimized for >99.8 transmission at 257 or 266nm designed wavelengths, with  $\lambda/2$  or  $\lambda/4$  retardance options for each. Featuring a superior retardation tolerance and zero-order construction, these waveplates have increased bandwidth and lower sensitivity to temperature change. DUV Vacuum-Compatible Waveplates have the fast axis marked on the edge of the mount for easy identification and system integration. These waveplates are ideal for life-science and lithography applications which require a vacuum environment.