

## A photograph of three Nikon lenses, likely the 24-70mm f/2.8 ED SR IF lens, arranged diagonally on a dark, reflective surface. The lenses are black with silver accents and feature a distinctive orange-tinted front element. The background is a dark gradient, and the lenses are reflected on the surface below them.



☐ -    1    ☐ +    **C\$362<sup>.60</sup>**

[ADD TO CART](#)

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | C\$362.60 each                |
| Need More?     | <a href="#">Request Quote</a> |

## Product Downloads

## General

**Product Family:**

**Note:**  
It is recommended to use **C-Mount Camera Imaging Filters** when filters are required.

**Imaging Lens Type:**

## Physical & Mechanical Properties

|          |                               |
|----------|-------------------------------|
| Variable | Iris Option:                  |
|          |                               |
| 40.31    | Length (mm):                  |
|          |                               |
| 30.5     | Maximum Diameter (mm):        |
|          |                               |
| 30.5     | Outer Diameter (mm):          |
|          |                               |
| 0.00     | Maximum Rear Protrusion (mm): |
|          |                               |
| 40.58    | Maximum Length (mm):          |
|          |                               |

Optical Properties

|                      |                                               |
|----------------------|-----------------------------------------------|
| 59.1°                | Horizontal Field of View @ Max Sensor Format: |
|                      |                                               |
| 49.1°                | Horizontal Field of View, 1/1.8" Sensor:      |
|                      |                                               |
| 44.0°                | Horizontal Field of View, 1/2" Sensor:        |
|                      |                                               |
| 11.00                | Maximum Image Circle (mm):                    |
|                      |                                               |
| 0.003                | Numerical Aperture NA, Object Side:           |
|                      |                                               |
| 8 (7)                | Number of Elements (Groups):                  |
|                      |                                               |
| 400 - 700            | Wavelength Range (nm):                        |
|                      |                                               |
| 8.00                 | Focal Length FL (mm):                         |
|                      |                                               |
| 250 - ∞              | Working Distance (mm):                        |
|                      |                                               |
| f/4 - f/16           | Aperture (f/#):                               |
|                      |                                               |
| 0.747                | Back Focal Length BFL (mm):                   |
|                      |                                               |
| λ/4 MgF <sub>2</sub> | Coating:                                      |
|                      |                                               |
| 14.03                | Entrance Pupil Position (mm):                 |
|                      |                                               |
| 19.28                | Object Space Principal Plane (mm):            |
|                      |                                               |
| 9.25                 | Image Space Principal Plane (mm):             |
|                      |                                               |
| 2.88                 | Maximum Distortion (%):                       |
|                      |                                               |
| -5.40                | Exit Pupil Position (mm):                     |
|                      |                                               |
| VIS                  | Lens Wavelength Range:                        |
|                      |                                               |
| VIS                  | Wavelength:                                   |
|                      |                                               |

Sensor

|      |                          |
|------|--------------------------|
| 2/3" | Optimized Sensor Format: |
|      |                          |
| 2/3" | Maximum Sensor Format:   |
|      |                          |
| 2.74 | Pixel Size (μm):         |
|      |                          |

Threading & Mounting

|                    |                |
|--------------------|----------------|
| N/A                | Filter Thread: |
|                    |                |
| M28.0 x 0.5 (Male) | Front Thread:  |
|                    |                |
| C-Mount            | Mount:         |
|                    |                |

Environmental & Durability Factors

|                                                                                             |                           |
|---------------------------------------------------------------------------------------------|---------------------------|
| -20 to +60<br>For questions regarding operating temperature please contact our support team | Storage Temperature (°C): |
|                                                                                             |                           |

## Product Details

- Cost Effective Solution for Systems that Require Large Depth of Field
- Up to ⅔", C-Mount Lens
- Ideal for Logistics and Barcode Scanning Applications

Edmund Optics E Series Fixed Focal Length Lenses provide an affordable fixed focal length imaging solution without compromising performance. These lenses are designed for logistics applications that need to identify product size and shape, read barcodes, and help find product locations. These systems often don't require lenses designed with more demanding specifications like large format sensor coverage and small pixels, which can be costly. Edmund Optics E Series Fixed Focal Length Lenses are a balance of performance and cost designed with a maximum format of 2/3". To maintain affordability in prototyping and mass production, the lens housings have been simplified by removing focusing mechanics. However, the focus can still be adjusted by threading the lenses into and out of the camera, then locked with a locking ring. These lenses maintain performance control with an adjustable iris ranging from f/4 to f/16.