

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#) / [Basler ace2 GigE/5GigE Cameras](#)

[See all 53 Products in Family](#)

## Basler ace2 a2A5320-7gcPRO Color GigE Pro Camera



Basler ace2 GigE Cameras (Front)



Stock **#16-614** ☐ In Stock

[Similar Cameras](#)

1

C\$2,406.60

ADD TO CART

Qty 1+

C\$2,406.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Video Output:**  
GigE (PoE)

**Type:**  
Color Camera

**Manufacturer:**  
Basler

**Mounting Threads:**

1/4-20 with Tripod Mount Adapter [#16-641](#)

|                                                                                            |
|--------------------------------------------------------------------------------------------|
| <b>Image Buffer:</b><br>Not Specified                                                      |
| <b>Camera Family:</b><br>ace2                                                              |
| <b>Model Number:</b><br>a2A5320-7gcPRO                                                     |
| <b>Imaging Sensor:</b><br>Sony IMX542                                                      |
| <b>Type of Sensor:</b><br>Progressive Scan CMOS                                            |
| <b>Type of Shutter:</b><br>Global                                                          |
| <b>Camera Sensor Format:</b><br>1.1"                                                       |
| <b>Resolution (MegaPixels):</b><br>16.10                                                   |
| <b>Pixels (H x V):</b><br>5,320 x 3,032                                                    |
| <b>Pixel Size, H x V (µm):</b><br>2.74 x 2.74                                              |
| <b>Sensing Area, H x V (mm):</b><br>14.6 x 8.3                                             |
| <b>Frame Rate (fps):</b><br>7.00                                                           |
| <b>Pixel Depth:</b><br>8/10/12 bit                                                         |
| <b>Exposure Time:</b><br>Freely Programmable                                               |
| <b>Connector:</b><br>GigE, RJ45 with Screw Locks                                           |
| <b>Power Supply:</b><br>Power over Ethernet (PoE) or via GPIO with <a href="#">#16-644</a> |
| <b>Power Consumption (W):</b><br>4.0                                                       |
| <b>GPIOs:</b><br>1 opto-coupled input line, 2 general purpose I/O (GPIO) lines             |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO), Software Trigger, or Free-Run          |
| <b>Dimensions (mm):</b><br>55.5 x 29 x 29 (excludes connectors and lens mount)             |
| <b>Weight (g):</b><br><100                                                                 |
| <b>Mount:</b><br>C-Mount                                                                   |
| <b>Housing:</b><br>Full                                                                    |
| <b>Interface Port Orientation:</b><br>Back Panel                                           |
| <b>Dynamic Range (dB):</b><br>70.8                                                         |
| <b>Operating Temperature (°C):</b><br>-10 to +60                                           |
| <b>Storage Temperature (°C):</b><br>-20 to +80                                             |
| <b>GPIO Connector Type:</b><br>6-pin M8                                                    |
| <b>Machine Vision Standard:</b><br>GigE Vision 2.0, GenICam                                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |