

[See all 55 Products in Family](#)

# BFS-PGE-123S6P-C, Pol. PoE GigE Blackfly® S, Monochrome Camera

See More by [Teledyne FLIR](#)



Teledyne FLIR® IIS Blackfly® S GigE Cameras



+1

Stock **#22-082** 2 In Stock

-

1

+

C\$6,496<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | C\$6,496.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

Product Downloads

|                        |           |
|------------------------|-----------|
| Monochrome (Polarized) | Spectrum: |
|------------------------|-----------|

General

|                             |       |
|-----------------------------|-------|
| Polarized Monochrome Camera | Type: |
|-----------------------------|-------|

Model Number:

|                                                                                                                                                                                                                  |                             |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| BFS-PGE-123S6P-C                                                                                                                                                                                                 |                             |
| FLIR                                                                                                                                                                                                             | Manufacturer:               |
| Blackfly® S                                                                                                                                                                                                      | Camera Series:              |
| Physical & Mechanical Properties                                                                                                                                                                                 |                             |
| 29 x 29 x 30 (excludes connectors and lens mount)                                                                                                                                                                | Dimensions (mm):            |
| 36                                                                                                                                                                                                               | Weight (g):                 |
| Full                                                                                                                                                                                                             | Housing:                    |
| Sensor                                                                                                                                                                                                           |                             |
| 240MB                                                                                                                                                                                                            | Image Buffer:               |
| 1.1"                                                                                                                                                                                                             | Sensor Format:              |
| 12.30                                                                                                                                                                                                            | Resolution (Megapixels):    |
| 10.00                                                                                                                                                                                                            | Frame Rate (fps):           |
| 4,096 x 3,000                                                                                                                                                                                                    | Pixels (H x V):             |
| 3.45 x 3.45                                                                                                                                                                                                      | Pixel Size, H x V (µm):     |
| 14.13 x 10.35                                                                                                                                                                                                    | Sensing Area, H x V (mm):   |
| Sony IMX253MZR                                                                                                                                                                                                   | Imaging Sensor:             |
| Progressive Scan CMOS                                                                                                                                                                                            | Type of Sensor:             |
| Global                                                                                                                                                                                                           | Shutter Type:               |
| 10/12 bit                                                                                                                                                                                                        | Pixel Depth:                |
| 36µs to 30s                                                                                                                                                                                                      | Exposure Time:              |
| 70.77                                                                                                                                                                                                            | Dynamic Range (dB):         |
| GigE Vision v1.2                                                                                                                                                                                                 | Machine Vision Standard:    |
| Electrical                                                                                                                                                                                                       |                             |
| 2.5                                                                                                                                                                                                              | Power Consumption (W):      |
| Hardware & Interface Connectivity                                                                                                                                                                                |                             |
| GigE (PoE)                                                                                                                                                                                                       | Interface:                  |
| GigE, RJ45 with Screw Locks                                                                                                                                                                                      | Connector:                  |
| Power Supply Required and Sold Separately if not using PoE:<br>USA: <a href="#">#88-063</a><br>Europe: <a href="#">#88-063</a><br>Japan: <a href="#">#88-063</a><br>Korea: Not Available<br>China: Not Available |                             |
| 1 opto-isolated input, 1 opto-isolated output, 1 non-isolated bi-directional, 1 non-isolated input                                                                                                               | GPIOs:                      |
| Hardware Trigger (GPIO) or Software Trigger                                                                                                                                                                      | Synchronization:            |
| Back Panel                                                                                                                                                                                                       | Interface Port Orientation: |
| 6-pin Hirose (HR10)                                                                                                                                                                                              | GPIO Connector Type:        |
| Threading & Mounting                                                                                                                                                                                             |                             |
| C-Mount                                                                                                                                                                                                          | Mount:                      |
| 1/4-20 with Tripod MOUNT Adapter <a href="#">#88-210</a>                                                                                                                                                         | Mounting Threads:           |
| Environmental & Durability Factors                                                                                                                                                                               |                             |

|                       |                             |
|-----------------------|-----------------------------|
| 0 to +50              | Operating Temperature (°C): |
| -30 to +60            | Storage Temperature (°C):   |
| Regulatory Compliance |                             |
| Exempt                | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Contains SVHC(s)      | Reach 240:                  |

## Product Details

- PoE (Power over Ethernet)
- GigE Vision and GenICam Compliant
- Ultra Compact Form Factor
- Extensive API Library and Included Spinnaker SDK



### Teledyne FLIR IIS Blackfly S: Advanced Machine Vision Cameras with powerful features

Capture the images you need from advanced sensors in enclosed or board-level configurations

The **Blackfly® S** is a versatile and compact machine vision camera series that leverages the industry's most advanced area scan sensors in an ultra-compact form factor. It combines powerful features that easily produce the exact images required, accelerating application development. Combining both automatic and precise manual controls over image capture and on-camera pre-processing. With options ranging from high-speed performance, high-resolution images, polarization, or low-light sensitivity, the Blackfly® S series of cameras can deliver the required results.

With the selection of camera variations all sharing the same form factor, it makes it easy to develop once, deploy anywhere. On camera features include IEEE1588 clock synchronization and full compatibility with popular third-party software supporting either GigE Vision or USB3 Vision interfaces. The Blackfly® S is available in GigE, USB3, cased, and board-level versions.

Note: **GigE cable** sold separately and required for operation . Software available for **download**. **Blackfly® PoE GigE Cameras** are also available.

#### Blackfly® S GigE color / monochrome cameras

- On camera features include IEEE1588 clock synchronization and full compatibility with popular third-party software supporting GigE Vision. GigE models featuring Lossless Compression (LLC) are also available with higher maximum frame rates and lower bandwidth requirements, helping maximize output without compromising image quality.

#### Features

- Ultra-compact form factor (29mm x 29mm x 39mm)
- Leverage the latest CMOS sensors and new on-camera image processing features
- Harness increased binning flexibility, powerful auto-exposure controls and robust color transformation tools
- Improve cycle time using advanced camera controls and programmable logic
- Utilize sequencer, chunk data, event notification, counters, timers and logic blocks
- Choice of CMOS global shutter, polarization, and high-sensitivity BSI sensors
- Data interface options: GigE, USB3
- Color transformation tools for true-to-life color
- Advanced auto-algorithms or precise manual control over image capture and on-camera pre-processing
- On-camera features such as IEEE1588 clock synchronization, lossless compression, and deep learning inference
- Compatible with third-party software and hardware
- Support for a wide range of operating systems and host system architectures
- Rich sample code and descriptive API logging
- Simplified product iteration with consistent form factor across sensor sizes
- Camera control via FlyCapture SDK or 3rd-party USB3 Vision software

#### Applications

- Intelligent Transportation Systems
- Factory automation
- Bar code reading
- 3D scanning
- Life science instrumentation
- Biometrics kiosk solutions
- Ophthalmoscopy
- Automated optical inspection
- Food & Beverage industry

## Calibration Services