

[See all 14 Products in Family](#)

Everix Ultra-Thin OD 2 Bandpass Filter, 810nm, 12.5mm Dia.

See More by [Everix](#)



Stock **#16-839** 16 In Stock

-

1

+

C\$107¹⁰

ADD TO CART

Volume Pricing	
Qty 1-10	C\$107.10 each
Qty 11+	C\$94.50 each
Need More?	Request Quote

Product Downloads

General

Type:

Flexible Filter

Physical & Mechanical Properties

Diameter (mm):

12.45 ±0.15

Clear Aperture (%):

>90

Maximum Thickness (µm):

Optical Properties

2.0	Optical Density OD (Average):
810.00	Center Wavelength CWL (nm):
33.10 (maximum)	Full Width-Half Max FWHM (nm):
>65% Average	Transmission (%):
±2	Center Wavelength CWL Tolerance (%):

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Designed for Common LED and Laser Diode Wavelengths
- Scratch Insensitive, Ultra-Thin Design
- Easily Integrated into Portable Devices

Everix Ultra-Thin Broadband Bandpass Filters are designed for common LED and laser diode wavelengths. With an exterior polymeric protective layer, these filters are scratch-insensitive, shatterproof, and easy to clean. These filters feature an average transmission of 65%, average optical density of 2.0, and maximum thickness of 400 μm. Ultra-Thin Broadband Bandpass Filters are created with a lightweight, ultra-thin design and can be easily integrated into portable systems, including point of care medical devices, AR/VR wearables, and spaceborne systems.

For more information on this patented ultra-thin filter technology, visit our [Everix brand page](#).

Note: Custom filter designs can be purchased directly from [Everix](#).

Technical Information

