

[See all 12 Products in Family](#)

BladeCam2-HR-TEL Beam Profiler



Stock **#29-186** **1 In Stock**

-

1

+

C\$7,238^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$7,238.00 each
Need More?	Request Quote

Product Downloads

General

Model Number:

S-BC2-HR-TEL

Physical & Mechanical Properties

Dimensions (mm):

46 x 46 x 16.5

Dimensional Accuracy:

0.1 µm

Optical Properties

Spectral Range:

1480 - 1605	
52 (min)	Beam Diameter (µm):
Sensor	
5.2 x 5.2	Pixel Size, H x V (µm):
1,280 x 1,024	Pixels (H x V):
6.6 x 5.3	Sensing Area, H x V (mm):
1/2"	Sensor Format:
≥9	Frame Rate:
Electrical	
1,000:1	Signal to Noise S/N Ratio (dB):
30 dB optical / 60 dB electrical	Peak Noise (nW/cm²):
Threading & Mounting	
Mount: 6-32 holes aligned with sensor center. 4-40 holes on camera rear. NOTE: DataRay will ship new units with a 1/4"-20 adapter. Please contact us if adapters are needed for existing consignment units.	
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Designed for Use from 355 to 16000nm
- Compatible with Beam Diameters Down to 52µm
- Robust and Easy to Use Free Software [Provided](#)
- Measure Beam Wander, M², Divergence, and More

DataRay Camera Beam Profilers provide excellent solutions for beam analysis of both continuous wave and pulsed laser sources. Each beam profiler features an integrated CMOS sensor (IR profilers feature Microbolometer sensors) that eliminates comet trailing for higher resolution output and allows for update rates of 60+ Hz. Sensors are available with active sizes of 6.6, 11.3, and 25mm horizontals, enabling measurement of large beam diameters. DataRay Camera Beam Profilers have the added advantage of a free, robust software with analysis features such as M² measurement, beam wander and logging, and instrument alignment. These profilers are USB3.0/2.0 powered and include a 3m flexible screw locking cable. Neutral density filters with optical densities of 1.0, 2.0, and 4.0 are included.