

Fiber Spatial Filter-FC



Fiber Spatial Filter-FC, #55-475

Stock **#55-475 2 In Stock**

⊖ 1 ⊕ C\$1,834⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$1,834.00 each
Need More?	Request Quote

Product Downloads

General

Adjustable - Linear (XYZ) & Tip-Tilt **Type:**

Fiber Connector **Type of Optics:**

10X microscope objective included **Note:**

Physical & Mechanical Properties

Black Anodized Aluminum **Construction:**

XY: ±1.5, Z: ±5	Linear Travel (mm):
2.5 (XY)	Linear Travel Resolution (µm):
±2	Tip/Tilt Angle (°):
±2	Base Tilt Angle (°):

Electrical

FC	Fiber Connection:
----	--------------------------

Hardware & Interface Connectivity

Differential Micrometer (XY)	Type of Drive:
------------------------------	-----------------------

Threading & Mounting

M6 x 1.0	Compatible Post:
----------	-------------------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

- X-Y Micrometer Translation
- Gimbal Tilt Control for Fiber Alignment
- Z-Axis Translation for Objective Mount

Our Metric Spatial Filters are designed to ease [fiber optic](#) and [pinhole](#) system integration. With ±1.5mm micrometer driven X-Y translation, 2.5µm resolution, and an objective mount with 10mm Z-axis translation, these Metric Spatial Filters are ideal for a range of DIN and JIS standard [objectives](#). The fiber optic metric spatial filter provides easy connection for fiber optics with an FC termination and features gimbal tilt control for fiber alignment with a ±2° adjustable angle range. The pinhole metric spatial filter includes a pinhole adapter for integrating mounted and unmounted pinholes.

Note: Metric Spatial Filters are only compatible with the following objectives: DIN Achromatic 4X ([#43-902](#)), DIN Plan 4X ([#67-706](#)), and the JIS Achromatic 10X.

Technical Information

