

TECHSPEC[®] Filter Adapter M58 x 0.75 from M40 x 0.5 (Female)



Filter Adapter M58 x0.75 from M40 x0.5 (Female)



Stock **#87-425** 20+ In Stock

-

1

+

C\$84^{.70}

ADD TO CART

Volume Pricing	
Qty 1+	C\$84.70 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

Lens Accessory

Threading & Mounting

Filter Thread:

M58 x0.75 (Female)

Regulatory Compliance

Certificate of Conformance:

[View](#)

PRODUCT DETAILS

- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Compact (C) Broadband Lens for 425-1000nm Wavelength Range
- 3.5mm to 50mm Focal Length

TECHSPEC® C Series Fixed Focal Length VIS-NIR Lenses are designed for use in machine vision applications that require NIR or VIS-NIR performance, with the working distance and resolution requirements of factory automation and inspection in mind. Featuring large maximum apertures and a Broadband Anti-Reflection (BBAR) coating designed out to 1000nm, these high performance lenses can be used in even the most restrictive lighting conditions. TECHSPEC® C Series Fixed Focal Length VIS-NIR Lenses are manufactured to a high tolerance, resulting in greater levels of imaging performance and low lens-to-lens variation, assuring simple installing into multiple systems. By combining high optical performance, industrial features, and small package size, the C Series Fixed Focal Length VIS-NIR Lenses represent a new standard in factory automation optics.

Also available with a [VIS Broadband Anti-Reflection \(BBAR\)](#) or [SWIR](#) Coatings

Note: For IR imaging alone, [UV-VIS Cut Filters](#) are available and thread directly onto the front filter threads of the 4.5mm, 16mm, 25mm, 35mm and 50mm FL lenses.

TECHNICAL INFORMATION

