

[See all 2 Products in Family](#)

Sekonic C-4000 Spectrometer Light Meter



Stock **#75-460** NEW **1 In Stock**

-

1

+

C\$1,398⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,398.60 each
Need More?	Request Quote

Product Downloads

General	
5 - 10,000 Lux, 0.46 to 929 footcandles	Range:
C-4000	Model Number:
C-4000 Spectrometer Light Receptor Cap Soft Case *Requires Batteries or USB-c cable for Operation	Contents of Kit:

Units: Correlated Color Temperature (Tcp), Deviation (Δuv), CRI (Ra), TM-30 (Rf, Rg), CIE 1931 (x, y), Illuminance (lx or fc)	
Response Time (s): Max.: 15 sec., Min.: 2 sec.	
Physical & Mechanical Properties	
Weight (g): 140 (without batteries)	
Dimensions (mm): 62 × 140 × 30	
Accuracy (%): Illuminance: ±5 % ±1 digit (5 lx to 3,000 lx), ±7.5 % ±1 digit (over 3,000 lx); x, y: ±0.003 (800 lx)	
Optical Properties	
Wavelength Range (nm): 380 - 780	
Sensor	
Type of Sensor: CMOS linear image sensor	
Hardware & Interface Connectivity	
Power Supply: 2 x 1.5V Alkaline Batteries, USB Power	
Environmental & Durability Factors	
Operating Temperature (°C): +5 to +35, without condensation	
Storage Temperature (°C): -10 to +60 , without condensation	
Additional Info	
Display Language: English, French, German, Italian, Spanish, Japanese	
Compatibility: Connect to PC via USB Cable; Bluetooth connectivity via Smart device (Apple or Android)	
Regulatory Compliance	
RoHS 2015: Compliant	
Certificate of Conformance: View	
Reach 247: Compliant	

Product Details

▶

Video

Sekonic C-4000 Sekonic LD FREE App Tour

Watch 

▶

Video

Sekonic C-4000 Sekonic LD PAID App Tour

Watch 

- Able to Measure LED, Fluorescent, Flash, and Natural Light
- Handheld and Portable for Ease of Use
- Ideal for Measuring Light in Industrial and Scientific Environments

Sekonic Spectrometer Light Meters are compact, handheld instruments designed for precise light and color measurement in industrial and scientific environments. Combining the capabilities of a spectrometer, light meter, and color meter, the Sekonic C-7000 and C-4000 models deliver accurate illuminance readings, color parameters, spectral characteristics, and more. The C-4000 is optimized for on-site use, offering a user-friendly interface and essential spectral data collection—ideal for basic lighting evaluations in industrial settings. The more advanced C-7000 features higher resolution, extended measurement capabilities, and advanced data logging capabilities for detailed analysis and quality control. Sekonic Spectrometer Light Meters are trusted across many applications such as display calibration in manufacturing, light monitoring in life science experiments, and illumination control in defense and aerospace systems.

What do Sekonic spectrometer light meters measure?
They measure illuminance, color parameters, and spectral distribution from various light sources, including LED, fluorescent, and natural light.

What are the main differences between the C-7000 and C-4000 models?
The C-4000 is great for quick, on-site evaluations with essential spectral data. The C-7000 offers more measurement capabilities, higher resolution, and advanced logging options. Both provide measurement ranges of 380–780nm.

Can these meters be used for LED lighting?
Yes, both models are ideal for analyzing modern LED lighting systems in manufacturing, life sciences, and QA environments.

Are Sekonic meters color meters or exposure meters?
Both models function as Sekonic exposure meters, color meters, and spectrometers, providing comprehensive light and color analysis.

Do they support data export or computer connection?
Yes, both offer USB data export via PC or Mac. The C-4000 also offers Bluetooth connectivity via the Sekonic LD app for [iOS](#) and [Android](#). Depending on your region, you may not be able to download SEKONIC LD.

