

TECHSPEC® Finite Conjugate, Gold Coated, 20X/0.33NA ReflX Objective



Stock **#39-147** ☐ In Stock

- 1 + **C\$3,277.40**

ADD TO CART

Qty 1+
C\$3,277.40
Qty 2+
C\$2,948.40
Volume Pricing
Request Quote

Get Product Downloads

Entrance Pupil Position (mm):
7 (Diameter)

Horizontal Field of View, 1/2" Sensor:
0.32mm

Horizontal Field of View, 2/3" Sensor:
0.44mm

Focal Length FL (mm):
9.91

Coating: Protected Gold (700-11000nm)
Magnification: 20X
Numerical Aperture NA: 0.33
Mounting Threads: RMS
Type: Microscope Objective
Obscuration (%): 30.46
Transmitted Wavefront, RMS: λ/10
Diameter of Small Mirror (mm): 8.4
Working Distance (mm): 18.88
Aperture Diameter (mm): 7.9
Coating Specification: Ravg >96% @700 - 11000nm (typical)
Wavelength Range (nm): 700 - 11000
Style: Finite Conjugate
Manufacturer: Edmund Optics®
Flange Distance (mm): 150

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View